

## Wall-Mount Monitor Arm - 20.4" (52 cm) Dual-Swivel Arm - Premium

Product ID: ARMWALLDSLP



Free up space with this wall-mount monitor arm and enjoy optimum viewing with the long dual-swivel extension arm. The premium design ensures smooth, effortless motion and makes it easy to re-position your display, to work in comfort or collaborate with others. The attractive silver finish complements your decor.

The wall-mount system is ideal for business, healthcare, financial or other settings, where you may want to share your screen, or for customer-facing interactive displays.





### **Adjust the Dual-Swivel Arm with Ease**

The wall-mount monitor arm extends a full 20.4" (52 cm) and has three swivel points, offering an extended range of motion. Move the dual-swivel arms left or right, to change your screen position. You can also adjust the swivel tension.

### **Durable and Stable Construction**

The robust aluminum design provides a stable wall-mount for your computer monitor or flat-screen TV up to 30". It's ideal for touch-screen stability. The universal display wall mount supports VESA mount monitors (75x75, 100x100) up to 30.9 lb. (14 kg) in weight.

### **Adjust your Viewing Angle**

Share your screen with ease. The display wall mount offers a full +180-degree/-180-degree pan, to move your screen left or right. It tilts freely +90/-15-degrees, to adjust the angle up or down. Rotate your screen for landscape or portrait viewing.



### **Low-Profile Design**

Push the swivel arm back to the wall, so your monitor sits just 5" (129 mm) from the wall when not in use.

### **Tool-less Assembly**

The quick slide-and-click connections make the monitor wall mount easy to assemble and saves time when setting up multiple units.

The TAA compliant ARMWALLDSLP is backed by a StarTech.com 5-year warranty and free lifetime technical support.

### Certifications, Reports and Compatibility



### Applications

- Free up space in business, commercial, industrial or office settings
- Share your screen with clients or visitors in office settings such as healthcare or financial
- Works well in non-desk environments as well as public places

### Features

- Wall-mount a single display up to 30" to save space and easily share your screen
- Long dual-swivel arm extends 20.4" (52 cm) and features three swivel points for flexible viewing
- Easy tool-less assembly with quick slide-and-click connections
- Adjust your viewing angle with +180°/-180° pan, +90°/-15°tilt, and rotation
- Robust and stable aluminum design supports VESA mount displays (75x75, 100x100) with maximum weight of 30.9 lb. (14 kg)

<b>Hardware</b>	Warranty	5 Years
	# of Displays Supported	1
	Articulating	No
	Cable Management	Yes
	Mounting Options	Wall-Mount
	VESA Hole Pattern(s)	75x75 mm 100x100 mm
<b>Performance</b>	Display Pan	+180° / -180°
	Display Rotation	360°
	Display Tilt	+90° / -15°
	Height Adjustment	No
	Maximum Arm Extension	20.5 in [520 mm]
	Maximum Display Size	30in
	Minimum Display Size	13"
	Swivel / Pivot	+180°/-180° at the wall 360° at the shoulder 360° at the elbow
<b>Physical Characteristics</b>	Weight Capacity (Per Display)	30.9 lb [14 kg]
	Color	Silver
	Enclosure Type	Aluminum
	Product Height	13 in [330 mm]
	Product Length	6.9 in [176 mm]
	Product Width	5.1 in [129 mm]
	Weight of Product	63.5 oz [1800 g]
<b>Packaging Information</b>	Package Height	3.9 in [100 mm]
	Package Length	13.4 in [340 mm]
	Package Width	9.4 in [240 mm]
	Shipping (Package) Weight	52.2 oz [1480 g]
<b>What's in the Box</b>	Included in Package	1 - Wall Mount 2 - Swivel Arms 1 - Monitor Mount

- 4 - Thumb Screws
- 1 - M3 Hex Key
- 2 - Wall Plugs
- 2 - Mounting Screws
- 1 - User Manual

---

Product appearance and specifications are subject to change without notice.