

## 2U Rack Blank Panel for 19in Server Racks and Cabinets

Product ID: BLANKB2



The BLANKB2 2U Rack Blank Panel for 19in Server Racks and Cabinets is designed to EIA RS-310-C specifications and fits all 19" standard server racks and cabinets.

Ideal for improving airflow within the rack by covering the unused spaces, the filler panel/blank panel is constructed of cold-rolled steel and features a black powder coated finish that matches most industry standard black server cabinets and racks.

**Certifications, Reports  
and Compatibility**



**Applications**

- Filling in the spaces when no other rack mounted equipment is needed
- Assist with directing air flow

**Features**

- SPCC Cold Rolled Steel, 1.2mm thick
- Powder black coloring to match most rack and cabinets

<b>Hardware</b>	Warranty	Lifetime
	Airflow Rate	Solid
	Frame Type	Steel
	Industry Standards	EIA RS310-C
	U Height	2U
<b>Physical Characteristics</b>	Color	Black
	Weight of Product	16.9 oz [479.9 g]
<b>Packaging Information</b>	Package Height	0.8 in [21 mm]
	Package Length	19.4 in [49.4 cm]
	Package Width	4 in [10.1 cm]
	Shipping (Package) Weight	19.2 oz [545 g]
<b>What's in the Box</b>	Included in Package	1 - 2 U Blanking Plate 1 - Package of M6 Screws and Cage nuts (4 sets)

Product appearance and specifications are subject to change without notice.