

Sit-Stand Desk Converter with Monitor Arm - 35" Wide Work Surface - For up to 26" Monitor

Product ID: BNDSTSLGSLIM



The sit-stand desk converter with single monitor arm helps enhance your productivity and comfort. This ergonomic desk solution includes two products: the spacious [sit-stand workstation](#) (ARMSTSLG) and the [articulating monitor mount](#) (ARMSLIM), supporting a display up to 26". The slim and stylish monitor arm frees up desk space and offers a full range of motion, adjusting easily for ideal viewing.



Go from sit to stand, with one touch

With one touch, switch your position from sitting to standing, to keep a balanced level of movement throughout the day. The height-adjustable standing desk workstation features a pneumatic spring that makes it easy to raise or lower your work surface up to 15.7" (400 mm), to suit your height requirements. You can also adjust the tension, to make height adjustments even easier.

Adjust your viewing angle

The articulating monitor arm makes it easy to adjust your display for perfect viewing. You can extend the arm up to 23.46" (596 mm) and tilt, pan, and swivel your display with a full range of motion. The arm's spring-assisted height adjustment allows easy positioning, with a maximum range of up to up to 14.17" (360 mm). The arm also rotates for landscape or portrait viewing.

Easy setup

Simply place the sit-stand desk converter on your existing desk (minimum 26" depth). Then, attach the monitor mount using the grommet hole and included grommet-mount hardware.

The BNDSTSLGSLIM is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Create a single monitor sit-stand workstation for business, corporate, institutional, or home office use
- Install ergonomic desk solutions while saving cost by utilizing existing desks and work spaces

Features

- Place the sit-stand workstation on your existing desk to create an ergonomic stand-up desk, with spacious 35" (0.9 m) wide work surface
- Lever-controlled pneumatic spring for easy height adjustment (max height adjustment range: 15.7")
- Single monitor mount supports one monitor up to 26", and offers wide range of height adjustment, up to 14.17" (360 mm)
- Articulating arm with wide range of motion (+90°/-65° tilt, 360° swivel at the elbow, and +/- 90° display rotation)
- Maximum arm extension of 23.46" (596 mm)
- Minimum footprint: 660 mm (26") D x 889 mm (35") W
- Sit-stand workstation features high-quality construction, engineered with steel and MDF wood base, tray and work surface
- Straight up and down movement, provides a stable workstation with no fear of tipping

Hardware	Warranty	2 Years
	# of Displays Supported	1
	Articulating	Yes
	Cable Management	Yes
	Mounting Options	Grommet Hole Mount
	VESA Hole Pattern(s)	75x75 mm 100x100 mm
	Wallmountable	No
Performance	Display Rotation	+/- 90°
	Height Adjustment	Yes
	Height Adjustment Range of Sit- Stand Workstation	15.7 in [399 mm] Height Adjustment Range of Monitor Arm: up to 14.17 in [360 mm] Weight Capacity of Work Surface: 28.1 lb [12.7 kg] Weight Capacity of Work Surface with Single Monitor Arm: 23.7 lb [10.7 kg]
	Maximum Arm Extension	23.5 in [596 mm]
	Maximum Display Size	26in
	Maximum Height	22 in [560 mm]
	Minimum Height	6.3 in [160 mm]
	Pan	360°
	Swivel / Pivot	180° around the support post 360° at the elbow
	Tilt	+90° / -65°
	Weight Capacity of Keyboard Tray	5.1 lb [2.3 kg]
Physical Characteristics	Color	Black
	Enclosure Type	Steel, MDF Wood and Plastic
	Keyboard Tray Depth	10.4 in [265 mm]
	Keyboard Tray Width	26.8 in [680 mm]
	Product Height	6.3 in [160 mm]
	Product Length	26.4 in [670 mm]
	Product Weight	44.3 lb [20.1 kg]
	Product Width	35 in [889 mm]

Packaging Information	Shipping (Package) Weight	58.2 lb [26.3 kg]
------------------------------	---------------------------	-------------------

Product appearance and specifications are subject to change without notice.