

## 24 Port 1U Rackmount Cat 6 110 Patch Panel

Product ID: C6PANEL24



The C6PANEL24 24-port 110-type Rack Mount Cat 6 Patch Panel is color coded for both T568A and T568B wiring providing the perfect solution for any voice or LAN application.

For hassle-free connections, the patch panel offers straight Cat 6 ports with 110-type termination, making it easy to insert and remove your cables. The 24-port patch panel also offers a quick and easy way to identify your cable runs, with port numbers clearly marked on the back of each RJ45 port, and a writeable/erasable marking surface for each port on the front of the panel for efficient system management.

Durably constructed of only top quality materials, this 24-port Network Patch Panel is backed by StarTech.com's 2-year warranty.

### Certifications, Reports and Compatibility



### Applications

- For installation in 19" rack/cabinets
- Suitable for applications that use 23-26 AWG solid state and standard network cables
- 1000BASE-T Gigabit Ethernet, 100BASE-TX Fast Ethernet, 10BASE-T Ethernet applications
- Voice, video and other applications

### Features

- Color coded for both T568A and T568B installations
- Terminated using 110-type punch tool
- Supports both Cat5e and Cat6 cables
- Writable and erasable marking surfaces for each port
- Meeting the ANSI/TIA-568-C.2 Category 6, ISO/IEC11801 and EN50173-1 specification

	Warranty	2 Years
<b>Special Notes / Requirements</b>	<b>Note</b>	IDC Contact : Phosphor Bronze with Tin Plating
<b>Environmental</b>	Humidity	10~65%
	Operating Temperature	-10~60°
<b>Physical Characteristics</b>	Color	Black
	Product Height	1.7 in [44 mm]
	Product Length	1.3 in [34 mm]
	Product Weight	20.5 oz [581 g]
	Product Width	19 in [483 mm]
<b>Packaging Information</b>	Package Quantity	1
	Shipping (Package) Weight	23.9 oz [678 g]
<b>What's in the Box</b>	Included in Package	1 - 24 Port 1U Rackmount Cat 6 110 Patch Panel
		4 - M6 Screws
		4 - M5 Screws

Product appearance and specifications are subject to change without notice.