

## 8-port KVM Module for Rack-Mount LCD Consoles

Product ID: CAB831HDU



This 8-port KVM module works with the StarTech.com series of rack-mounted LCD consoles, enabling you to control eight servers from one location. You can upgrade a single port LCD console or replace a faulty console (see our list of compatible LCD consoles below).

With independent VGA and USB keyboard and mouse ports, you can also use this switch as a standalone KVM, creating a discreet rack-mountable KVM solution

### **Increase your productivity**

By adding this KVM module to your rack mount LCD console you can control eight individual computers or servers from a centralized location.

### **Hassle-free integration**

Because the KVM module works with your existing LCD console, you can ensure simple integration into your server room setup. To ensure compatibility this KVM module supports any operating system has been extensively tested in Windows®, Mac and Linux environments.

You can also connect to USB servers using StarTech.com's convenient line of 2-in-1 USB KVM cables. The cables come in variety of lengths your specific requirements.

## Compatible LCD consoles

### North America

RACKCOND1701 *(add 8 port module)*

[RACKCONS1908](#) *(replace original module)*

[RACKCONS1916](#) *(replace original module)*

[RACKCONS1708](#) *(replace original module)*

[RACKCONS1716](#) *(replace original module)*

### United Kingdom

RACKCOND1701 *(add 8 port module)*

RKCONS1716GB *(replace original module)*

RKCONS1908GB *(replace original module)*

### Europe

RACKCOND1701 *(add 8 port module)*

RKCOND1701FR - French Keyboard *(add 8 port module)*

The CAB831HDU is TAA compliant and backed by a 2-year StarTech.com warranty with free lifetime technical support.

### Certifications, Reports and Compatibility



### Applications

- Add single console administration to your Co-location/ISP facility saving you time and money
- Perfect for manufacturing line computer control, simplifying access to multiple systems
- Great for PC test/burn-in computer control saving the desk space required for multiple monitors, keyboards and mice

### Features

- Controls up to 8 computers connected directly and up to 64 computers by cascading 8 additional KVM switches
- Integrated OSD (on-screen display) enables unique computer name assignment
- Compatible with PC, Mac® and Sun servers/systems
- Supports USB connection to Servers or PCs
- Operating system independent
- No software or drivers required
- Hot-pluggable allowing computers to be added or removed without shutting down
- Auto-Scan Mode lets you switch between computers for easy monitoring
- Login authentication restricts access to authorized users
- DDC2B compatible
- Supports IntelliMouse (Pro)
- Uses StarTech.com tangle-free KVM cables

<b>Hardware</b>	Warranty	3 Years
	Audio	No
	Daisy-Chain	Yes
	KVM Ports	8
	Number of Monitors Supported	1
	PC Interface	USB
	PC Video Type	VGA
	Rack-Mountable	Yes
	U Height	1U
<b>Performance</b>	Auto Scan	3, 8, 15 & 30 seconds
	DVI Support	No
	IP Control	No
	Maximum Analog Resolutions	1920x1440 @60Hz
	Maximum Cascaded Computers	64
	Maximum Number of Users	1
	MTBF	72,000 Hours
	On-Screen Display	Yes
	Port Selection Support	Hotkeys and OSD (On Screen Display)
Security Features	Per-Port Passwords	
<b>Connector(s)</b>	Console Interface(s)	1 - VGA (15 pin, High Density D-Sub) Female 2 - USB Type-A (4 pin) USB 2.0 Female
	Host Connectors	8 - VGA (15 pin, High Density D-Sub) Female
	Other Interface(s)	1 - Centronics (36 pin) Female
<b>Software</b>	OS Compatibility	OS independent; No software or drivers required
<b>Special Notes / Requirements</b>	<b>Note</b>	This product adds an 8 port KVM module to our 1UCABCONS, IUCABCONS17 or 1UCABCONS19 units, and is also compatible as a replacement KVM module for the RACKCONS1708, RACKCONS1716 and RACKCONS1916 Rack Mount LCD Consoles.
<b>Power</b>	Center Tip Polarity	Positive
	Input Current	1.8A
	Input Voltage	110V-240V AC
	Output Current	4A

	Output Voltage	12 DC
	Plug Type	M
	Power Source	Not Included (not required for standard applications)
<b>Environmental</b>	Humidity	80% RH
	Operating Temperature	5°C to 40°C (41°F to 104°F)
	Storage Temperature	-20°C to 60°C (-4°F to 140°F)
<b>Physical Characteristics</b>	Color	Black
	Enclosure Type	Steel
	Product Height	1.6 in [40 mm]
	Product Length	4.9 in [125 mm]
	Product Weight	3.3 lb [1.5 kg]
	Product Width	15.9 in [403 mm]
<b>Packaging Information</b>	Shipping (Package) Weight	4.7 lb [2.1 kg]
<b>What's in the Box</b>	Included in Package	1 - 8 Port KVM Module 1 - Bag, Mounting Screws 2 - Mounting Brackets

Product appearance and specifications are subject to change without notice.