

2U 22in Vented Rack Mount Shelf – Fixed Server Rack Cabinet Shelf - 50lbs / 22kg

Product ID: CABSHELF22V



The CABSHELF22V 2U 22in Depth Vented Rack Mount Shelf lets you add a compact, 2U shelf to virtually any standard 19-inch server rack or cabinet with front mount options. This TAA compliant product adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases.

Our vented rack shelves improve air flow and help to lower temperatures in the rack. Constructed using SPCC commercial grade cold-rolled steel, this durable fixed rack shelf can hold up to 22kg (50lbs) of equipment - a perfect solution for storing small, non-rackmount equipment, tools, peripherals or accessories in your rack to keep them readily accessible.

Backed by a StarTech.com Lifetime warranty.

Certifications, Reports and Compatibility



Applications

- Supply additional storage space for mission critical hardware and non-rack mount equipment
- For use with all 19" wide Server Racks and Cabinets

Features

- 2U Vented Rackmount Shelf
- Fits all standard 19" server racks
- TAA compliant for GSA Schedule purchases
- Holds up to 22kg (50lbs)
- SPCC 1.6mm Cold-rolled steel construction
- Front mount design

Hardware	Warranty	Lifetime
	Cable Management	No
	Frame Type	Steel
	Mounting Options	Front Mount (Front Only)
	U Height	2U
Performance	Weight Capacity (Stationary)	50 lb [22.6 kg]
Physical Characteristics	Color	Black
	Enclosure Type	Steel
	Product Weight	8 lb [3.6 kg]
	Rail Thickness	0.1 in [1.6 mm]
Packaging Information	Shipping (Package) Weight	10.3 lb [4.6 kg]
What's in the Box	Included in Package	1 - 2U 22in Depth Rack Shelf
		4 - M6 Screws
		4 - M6 Cage Nuts
		1 - Instruction Manual

Product appearance and specifications are subject to change without notice.