

2U Rack Mount Cantilever Shelf - 125lbs / 56kg - 18 in. Deep

Product ID: CABSHELFHD



The CABSHELFHD 2U 18in Depth Heavy Duty Fixed Rack Mount Shelf lets you add a high-capacity 2U shelf to virtually any standard 19-inch server rack or cabinet with front mount options. This TAA compliant product adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases.

This high-capacity server rack shelf is constructed using 2.3mm SPCC commercial grade cold-rolled steel, providing the additional strength required to hold up to 56kg (125lbs) of equipment - a perfect solution for storing larger, non-rackmount pieces of equipment, heavy tools or peripherals in your rack or cabinet.

Backed by a StarTech.com Lifetime warranty.

Certifications, Reports and Compatibility



Applications

- Supply additional storage space for heavy, mission critical hardware and non-rack mount equipment
- For use with all 19" wide Server Racks and Cabinets

Features

- 2U Heavy Duty Fixed Rackmount Shelf
- Fits all standard 19" server racks
- TAA compliant for GSA Schedule purchases
- Holds up to 56kg (125lbs)
- SPCC 2.3mm Cold-rolled steel construction
- Front mount design

Hardware	Warranty	Lifetime
	Cable Management	No
	Frame Type	Steel
	Mounting Options	Front Mount (Front Only)
	U Height	2U
Performance	Weight Capacity (Stationary)	125 lb [56.6 kg]
Physical Characteristics	Color	Black
	Enclosure Type	Steel
	Internal Depth	18 in [457.2 mm]
	Product Weight	11.4 lb [5.2 kg]
	Rail Thickness	0.1 in [2.3 mm]
Packaging Information	Shipping (Package) Weight	13.9 lb [6.3 kg]
What's in the Box	Included in Package	1 - 2U High Cap Rack Shelf
		8 - M6 Screws
		8 - M6 Cage Nuts
		1 - Instruction Manual

Product appearance and specifications are subject to change without notice.