

2U Vented Rack Mount Cantilever 2 Post Shelf - Mid/Center Mount Server Rack Cabinet Shelf - 150lbs / 68kg

Product ID: CABSHF2POSTV



The CABSHF2POSTV 2U Heavy Duty Mid-Mount Vented Rack Mount Shelf for 2 Post Racks allows you to add a high capacity mid-mount fixed shelf to almost any standard 2 post server rack. This TAA compliant product adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases.

The included mounting brackets can be adjusted to accommodate different post depths, making this 2U shelf a universal solution for 2 post rack storage, while the vented design helps to improve airflow in the rack. Constructed using 1.6mm SPCC commercial grade cold-rolled steel, this durable 2 post rack shelf can hold up to 67kg (150lbs) of equipment - a perfect solution for storing non-rackmount equipment, tools, peripherals or accessories in your rack to keep them readily accessible.

Backed by a StarTech.com Lifetime warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Supply additional storage space for mission critical hardware and non-rack mount equipment
- For use with all 19" wide, 2 Post Server Racks

Features

- 2U Vented 2 Post Rack Shelf
- Fits all standard 19" 2 Post racks
- TAA compliant for GSA Schedule purchases
- SPCC 1.6mm Cold-rolled steel construction
- Mid-mount design

Hardware	Warranty	Lifetime
	Cable Management	No
	Mounting Options	Mid-Mount
	U Height	2U
Performance	Weight Capacity (Stationary)	150 lb [67.9 kg]
Physical Characteristics	Enclosure Type	Steel
	Maximum Mounting Depth	6 in [152.4 mm]
	Minimum Mounting Depth	3 in [76.2 mm]
	Product Weight	9.1 lb [4.1 kg]
	Rail Thickness	0.1 in [1.6 mm]
Packaging Information	Shipping (Package) Weight	11.7 lb [5.3 kg]
What's in the Box	Included in Package	<ul style="list-style-type: none"> 1 - 2U Vented 2 Post Rack Shelf 4 - Brackets 8 - #10-32 UNF Cage Nuts 8 - #10-32 UNF Nuts 8 - #10-32 UNF, 3/8"L Screws 8 - #10-32 UNF, 5/8"L Panel Screws 1 - Instruction Manual

Product appearance and specifications are subject to change without notice.