

USB-C to VGA and HDMI Adapter - 2-in-1 - 4K 30Hz - Space Grey

Product ID: CDP2HDVGA



This USB-C to VGA and HDMI adapter offers a portable solution for connecting your USB Type-C laptop to a VGA or HDMI display. The multiport video adapter also works as a splitter, enabling you to simultaneously output an identical video signal to two separate monitors (1 x HDMI and 1 x VGA).

Two-in-One Video Connectivity with Travel in Mind

Avoid the hassle of carrying different adapters, with a 2-in-1 USB-C monitor adapter. With VGA, and HDMI outputs, you can conveniently connect your laptop to any HDMI or VGA-equipped display, using this multiport adapter.

The adapter features a durable aluminum enclosure and can withstand being carried in your travel bag.

Ultra HD 4K 30Hz Resolution

The HDMI output on this USB-C video adapter supports UHD resolutions up to 4K 30Hz, while the VGA output supports HD resolutions up to 1920 x 1200.

Stylish Connectivity for Your MacBook, MacBook Pro, or Any Laptop

The USB-C video adapter has a Space Gray housing and built-in USB-C cable designed to match your Space Gray MacBook or MacBook Pro. The adapter is compatible with USB-C DP Alt Mode devices.

CDP2HDVGA is backed by a StarTech.com 3-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Connect to virtually any VGA or HDMI display while traveling
- Use as a video splitter to output an identical image to a VGA and HDMI monitor simultaneously splitting the image
- Output video to a secondary VGA, or HDMI monitor

Features

- Maximize your laptop's video compatibility with a 2-in-1 adapter: USB-C to HDMI® and VGA
- Support resource-demanding applications with UHD resolutions up to 4K 30Hz
- Space Gray adapter matches your Space Gray MacBook or MacBook Pro

Hardware	Warranty	3 Years
	Active or Passive Adapter	Active
	Adapter Style	Adapters
	AV Input	USB Type-C
	AV Output	HDMI VGA
	Chipset ID	ITE - IT6222
Performance	Audio Specifications	HDMI output: 5.1 surround sound
	Maximum Analog Resolutions	1920 x 1200 @ 60Hz (VGA)
	Maximum Digital Resolutions	3840 x 2160 @ 30Hz (HDMI)
	Supported Resolutions	Maximum HDMI output: 3840 x 2160 @ 30Hz Maximum VGA output: 1920 x 1200 @ 60Hz <i>Lower resolutions and refresh rates may also be supported</i>
	Video Revision	HDMI 2.0
Connector(s)	Connector A	1 - USB-C (24 pin) DisplayPort Alt Mode Male Input
	Connector B	1 - VGA (15 pin, High Density D-Sub) Female Output 1 - HDMI (19 pin) Female Output
Special Notes / Requirements	Note	HDMI and VGA can output video at the same time. If both video outputs are connected, they'll display the same image at a maximum resolution of 1920x1200 @ 60Hz
Environmental	Humidity	5~90% RH
	Operating Temperature	0°C to 45°C (32°F to 113°F)
	Storage Temperature	-10°C to 70°C (14°F to 158°F)
Physical Characteristics	Accent Color	Black
	Cable Length	6.6 in [167 mm]
	Color	Space Gray
	Enclosure Type	Aluminum and Plastic
	Product Height	0.6 in [1.5 cm]
	Product Length	8.1 in [205 mm]
	Product Width	2.4 in [62 mm]
	Weight of Product	1.5 oz [43 g]

Packaging Information	Package Height	0.8 in [20 mm]
	Package Length	7 in [17.9 cm]
	Package Width	3.1 in [8 cm]
	Shipping (Package) Weight	0.1 lb [0.1 kg]
What's in the Box	Included in Package	1 - Travel A/V Adapter

Product appearance and specifications are subject to change without notice.