


6 ft. (1.8 m) USB-C to Mini DisplayPort Cable - 4K 60Hz - Black

Product ID: CDP2MDPMM6B



This USB-C to Mini DisplayPort cable lets you connect your Thunderbolt 3 or USB Type-C enabled device to a Mini DP monitor with just one cable, for a convenient, clutter-free connection.

Astonishing Picture Quality

Harness the video capabilities that are built into your USB-C connection. The USB Type-C to Mini DisplayPort cable delivers the astonishing quality of Ultra HD to your 4K display, at resolutions up to 3840 x 2160. Plus, the adapter is backward compatible with 1080p displays, which makes it a great accessory for home, office or other work environments.

Clutter-Free Installation

At 6 ft. (1.8 m) in length, this Mini DP cable delivers a compact connection that eliminates excess adapters and cabling, ensuring a tidy, professional installation. For shorter installations, we also offer a 1 m (3.3 ft.) USB C to mDP cable, enabling you to choose the right cable length for your custom installation needs.

Hassle-Free Setup

For easy operation and installation, this USB 3.1 Type-C to Mini DP adapter cable supports plug-and-play installation on both Windows and Mac computers.

CDP2MDPMM6B is backed by a 3-year StarTech.com warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Connect your MacBook or USB-C device to an mDP monitor
- Ideal for home office or hot desk environments
- Deliver enriched presentations on the go
- Experience crisp visuals with support for 4K 60Hz

Features

- Reduce clutter with a USB-C to mDP adapter and cable in one
- Get astonishing picture quality with support for UHD video resolutions up to 4K 60Hz
- Hassle-free connectivity with the reversible USB-C connector
- Make the perfect connection with a Mini DisplayPort cable that works with any USB Type-C enabled device
- Compatible with Thunderbolt 3 and USB 3.1 Type-C ports that support DP Alt Mode

Hardware	Warranty	3 Years
	Adapter Style	Cable Adapters
	AV Input	USB-C
	AV Output	Mini-DisplayPort
	Chipset ID	STMicroelectronics - STM32F072CUB6
	Ports	1
Performance	Audio Specifications	7.1 surround sound
	Maximum Digital Resolutions	3840x2160 @ 60 Hz
	Supported Resolutions	1024x768 1280x720 (High-definition 720p) 1920x1080 (High-definition 1080p) 1920x1200 2560x1440 2560x1600 3840x2160 (Ultra HD 4K)
	Wide Screen Supported	Yes
Connector(s)	Connector A	1 - USB-C (24 pin) DisplayPort Alt Mode Male Input
	Connector B	1 - Mini-DisplayPort (20 pin) Male Output
Special Notes / Requirements	Note	Your USB-C port must support DisplayPort over USB-C (DP Alt mode) in order to work with this adapter.
Environmental	Humidity	25%-60%RH
	Operating Temperature	5°C to 35°C (41°F to 95°F)
	Storage Temperature	-20°C to 60°C (-4°F to 140°F)
Physical Characteristics	Cable Length	6 ft [1.8 m]
	Color	Black
	Product Height	0.4 in [1 cm]
	Product Length	8.5 in [21.5 cm]
	Product Width	0.8 in [20 mm]
	Weight of Product	2 oz [58 g]
Packaging Information	Package Height	0.3 in [8 mm]
	Package Length	8.7 in [22 cm]
	Package Width	0.5 in [12 mm]
	Shipping (Package) Weight	0.1 lb [0.1 kg]
What's in the Box	Included in Package	1 - USB-C to Mini DisplayPort cable

Product appearance and specifications are subject to change without notice.