

1.8 m (6 ft.) USB-C to Mini DisplayPort Cable - 4K 60Hz - Black

Product ID: CDP2MDPMM6B



This USB-C™ to Mini DisplayPort adapter cable offers a convenient solution for directly connecting your DisplayPort over USB Type-C™ device to your Mini DP monitor. The adapter offers a connection distance of up to 1.8 m (6 ft.) and works with USB-C devices that support DP Alt Mode, such as the MacBook, Chromebook Pixel™ and Dell™ XPS™ models 15 and 13. It's also compatible with Thunderbolt™ 3 ports.

Clutter-free installation

At 1.8 m (6 ft.) in length, this adapter cable delivers a direct connection that eliminates excess adapters and cabling, ensuring a tidy, professional installation.

For shorter installations, StarTech.com also offers a [1 m \(3 ft.\) USB-C to Mini DisplayPort cable \(CDP2MDPMM1MB\)](#), enabling you to choose the right cable length for your custom installation needs.

Astonishing picture quality

At four times the resolution of high-definition 1080p, you'll be amazed at the picture quality of a 4K 60Hz monitor or television. This adapter cable lets you harness the video capabilities that are built into your USB Type-C connection, to deliver the astonishing quality of Ultra HD to your 4K display.

Plus, the adapter is still compatible with lower display resolutions, such as 1080p, which makes it a great accessory for your current home, office or other HD work environment, while future-proofing for 4K 60Hz implementation.

The CDP2MDPMM6B is backed by a 2-year StarTech.com warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Connect your BYOD MacBook or Dell XPS with USB-C to a provided Mini DisplayPort monitor at work
- Connect an mDP display to your USB-C laptop to use as a secondary display
- Connect a secondary USB-C laptop to the mDP port on your 2009 or 2010 iMac, to use your iMac as a monitor

Features

- Reduce clutter with a 1.8 m (6 ft.) all-in-one solution with a combined cable and adapter
- Astonishing video quality with support for resolutions up to 4K at 60Hz

Hardware	Warranty	2 Years
	Adapter Style	Cable Adapters
	AV Input	USB Type-C
	AV Output	Mini-DisplayPort
	Chipset ID	STMicroelectronics - STM32F072C8U6
	Ports	1
Performance	Audio Specifications	7.1 surround sound
	Maximum Digital Resolutions	3840x2160 @ 60 Hz
	Supported Resolutions	1024x768 1280x720 (High-definition 720p) 1920x1080 (High-definition 1080p) 1920x1200 2560x1440 2560x1600 3840x2160 (Ultra HD 4K)
	Wide Screen Supported	Yes
Connector(s)	Connector A	1 - USB-C (24 pin) DisplayPort Alt Mode Male Input
	Connector B	1 - Mini-DisplayPort (20 pin) Male Output
Special Notes / Requirements	Note	Your USB-C port must support DisplayPort over USB-C (DP Alt mode) in order to work with this adapter.
Environmental	Humidity	25%-60%RH
	Operating Temperature	5°C to 35°C (41°F to 95°F)
	Storage Temperature	-20°C to 60°C (-4°F to 140°F)
Physical Characteristics	Cable Length	6 ft [1.8 m]
	Color	Black
	Product Height	0.4 in [10 mm]
	Product Length	6 ft [1.8 m]
	Product Weight	1.6 oz [45 g]
	Product Width	0.8 in [20 mm]
Packaging Information	Shipping (Package) Weight	0.1 lb [0 kg]
What's in the Box	Included in Package	1 - USB-C to Mini DisplayPort cable

Product appearance and specifications are subject to change without notice.