

USB-C Multiport Video Adapter - 3-in-1 - 4K 30Hz - Black

Product ID: CDPVGDVHDBP



This USB-C™ multiport video adapter offers a portable solution for connecting your USB Type-C laptop to a VGA, DVI or HDMI® display.

All-in-One Video Connectivity, with Travel in Mind

Avoid the hassle of carrying different adapters for different displays with this 3-in-1 USB-C adapter. With VGA, DVI and HDMI output, you can connect your laptop to virtually any display.

Astonishing Picture Quality

The HDMI output on this USB-C video adapter supports UHD 4K resolutions, providing four times the picture quality of high-definition 1080p. All of the outputs (HDMI, VGA, DVI) can support high-definition resolutions of up to 1920 x 1200.

Maximum Portability

The convenient plug-and-play USB-C dongle is the perfect travel accessory. Fitting easily into your laptop bag, and offering three video output options, the USB-C display adapter is an ideal solution for Bring Your Own Device (BYOD) applications, wherever you go.

The CDPVGDVHDBP is backed by a StarTech.com 3-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Connect to virtually any display while traveling
- Connect your BYOD laptop to a provided VGA, DVI or HDMI display at work or school
- Connect a VGA, DVI or HDMI monitor to your USB-C computer to use as a secondary monitor

Features

- Maximize your video compatibility with a 3-in-1 USB-C display adapter: USB-C to VGA, DVI, or HDMI
- Get astonishing picture quality with support for UHD resolutions up to 4K 30Hz
- Thunderbolt™ 3 and USB Type-C™ with DP Alt Mode Compatible
- Easy to set up, use, and store

Hardware	Warranty	3 Years
	Active or Passive Adapter	Active
	Adapter Style	Adapters
	AV Input	USB Type-C
	AV Output	DVI HDMI VGA
Performance	Audio Specifications	HDMI output - 7.1 surround sound DVI output - 2-channel stereo audio
	General Specifications	Only one video output is supported on the video adapter at a time. If multiple connections are made, only one of the outputs will function.
	Maximum Analog Resolutions	1920 x 1200 @ 60Hz
	Maximum Digital Resolutions	3840 x 2160 @ 30Hz
	Supported Resolutions	HDMI output: 3840 x 2160 (@ 30 Hz), 2560 x 1600, 2048 x 1280 (@ 60 Hz), 1920 x 1200, 1920 x 1080, 1280 x 720 VGA and DVI output: 1920 x 1200 (@ 60 Hz), 1920 x 1080, 1280 x 720
	Video Revision	DisplayPort 1.2
Wide Screen Supported	Yes	
Connector(s)	Connector A	1 - USB-C (24 pin) DisplayPort Alt Mode Male Input
	Connector B	1 - HDMI (19 pin) Female Output 1 - DVI-I (29 pin) Female Output 1 - VGA (15 pin, High Density D-Sub) Female Output
Special Notes / Requirements	System and Cable Requirements	Your USB-C port must support DisplayPort over USB-C (DP Alt mode) in order to work with this adapter.
Environmental	Humidity	Storage: 5% ~ 90 % RH (no condensation) Operating: 10% ~ 85 % RH (no condensation)
	Operating Temperature	0°C to 45°C (32°F to 113°F)
	Storage Temperature	-10°C to 70°C (14°F to 158°F)
Physical Characteristics	Cable Length	5.9 in [150 mm]
	Color	Black
	Product Height	0.6 in [15 mm]

	Product Length	1.8 in [45 mm]
	Product Weight	1.8 oz [51 g]
	Product Width	3.3 in [85 mm]
Packaging Information	Shipping (Package) Weight	1.9 oz [55 g]
What's in the Box	Included in Package	1 - USB-C travel adapter

Product appearance and specifications are subject to change without notice.