

Aluminum Travel A/V Adapter: 4-in-1 USB-C to VGA, DVI, HDMI or mDP - 4K

Product ID: CDPVGDVHMDMP



This silver USB-C™ multiport video adapter offers a portable solution for connecting your USB Type-C laptop to a VGA, DVI, HDMI® or Mini DisplayPort display. The adapter is also available in Space Gray (CDPVDHMDPSG) and Rose Gold (CDPVDHMDPRG).



All-in-One Video Connectivity with Travel in Mind

Avoid the hassle of carrying different adapters for different displays with this 4-in-1 USB-C adapter. With VGA, DVI, HDMI and mDP output, you can connect your laptop to virtually any display, a convenient plug-and-play solution for travel or Bring Your Own Device (BYOD) applications.



Astonishing Picture Quality

The HDMI and mDP outputs on this USB-C video adapter support UHD 4K resolutions, providing four times the picture quality of high-definition 1080p. All of the outputs (HDMI, mDP, VGA, DVI) can support high-definition resolutions of up to 1920 x 1200.



Stylish Connectivity

The USB Type-C adapter has an aluminum housing designed to match your silver MacBook and is compatible with any device that supports USB-C DP Alt Mode. Featuring a built-in USB-C cable with magnetic cable manager, the USB-C video adapter conveniently stores away for easy travel.

The CDPVGDVHDM DP is backed by a StarTech.com 3-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Connect to virtually any display while traveling
- Connect your BYOD MacBook to a VGA, DVI, HDMI or mDP display at work or school
- Connect a secondary VGA, DVI, HDMI or mDP monitor to your MacBook

Features

- Maximize your video compatibility with a 4-in-1 adapter: USB-C to VGA, DVI, HDMI or Mini DisplayPort
- Get astonishing picture quality with support for UHD resolutions up to 4K 30Hz
- Make the perfect connection, with a USB-C adapter that exactly matches your silver MacBook
- Maximum portability with built-in magnetic cable manager and a durable aluminum housing

Hardware	Warranty	3 Years
	Active or Passive Adapter	Active
	Adapter Style	Adapters
	AV Input	USB Type-C
	AV Output	DVI HDMI VGA Mini-DisplayPort
	Chipset ID	Cypress - CYPD1120 Cypress - CY7C65210 Parade - PS8348B Parade - PS171
Performance	Audio Specifications	HDMI and mDP output - 7.1 surround sound
	General Specifications	Only one video output is supported on the video adapter at a time. If multiple connections are made, only one of the outputs will function.
	Maximum Analog Resolutions	1920 x 1200 @ 60Hz
	Maximum Digital Resolutions	3840 x 2160 @ 30Hz
	Supported Resolutions	Max HDMI output: 3840 x 2160 @ 30Hz Max mDP output: 3840 x 2160 @ 60Hz HDMI and mDP output: 3840 x 2160, 2560 x 1600, 1920 x 1200, 1920 x 1080, 1280 x 720 DVI and VGA output: 1920 x 1200, 1920 x 1080, 1280 x 720
	Video Revision	DisplayPort 1.2 HDMI 1.4
Wide Screen Supported	Yes	
Connector(s)	Connector A	1 - USB-C (24 pin) DisplayPort Alt Mode Male Input
	Connector B	1 - Mini-DisplayPort (20 pin) Female Output 1 - VGA (15 pin, High Density D-Sub) Female Output 1 - DVI-D (25 pin) Female Output 1 - HDMI (19 pin) Female Output
Special Notes / Requirements	System and Cable Requirements	Your USB-C port must support DisplayPort over USB-C (DP Alt mode) in order to work with this adapter.

Environmental	Humidity	40%-50%RH
	Operating Temperature	0°C to 70°C (32°F to 158°F)
	Storage Temperature	-10°C to 80°C (14°F to 176°F)
Physical Characteristics	Cable Length	4.3 in [110 mm]
	Color	Silver
	Product Height	0.6 in [1.5 cm]
	Product Length	4.1 in [10.5 cm]
	Product Width	2.2 in [55 mm]
	Weight of Product	3.8 oz [108 g]
Packaging Information	Package Height	1.2 in [30 mm]
	Package Length	6.7 in [17 cm]
	Package Width	5.7 in [14.5 cm]
	Shipping (Package) Weight	6.5 oz [184 g]
What's in the Box	Included in Package	1 - travel A/V adapter

Product appearance and specifications are subject to change without notice.