

# 1U Brush Strip Horizontal Server Rack Cable Management Panel

Product ID: CMBRUSH1U



The CMBRUSH1U Brush Strip Cable Management Panel mounts to a standard 19" 2 or 4-post rack to organize cables while keeping dust and dirt out of the rack. This TAA compliant product adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases.

Constructed of high-quality steel with high-density nylon bristles, the 1U brush plate creates a clean looking point of entry and offers cable separation for simple cable organization. The brush panel also promotes proper airflow through the rack by closing off open spaces between equipment.

For easy installation, this cable organizer comes complete with 2 sets of rack screws (10/32 and 12/24).

Backed by a StarTech.com 2-year warranty.

### Certifications, Reports and Compatibility



### Applications

- Use with server racks and cabinets, structured wiring closets and network distribution cabling to keep cables neat and tidy

### Features

- High-density nylon brush
- Takes up only 1U of rack space
- TAA compliant for GSA Schedule purchases
- Sturdy steel construction
- Mounts to standard 19" 2 or 4-post server racks
- Includes rack screws

<b>Hardware</b>	Warranty	2 Years
	Industry Standards	EIA RS310-D
	Mounting Options	Front Mount (Front Only)
	Orientation	Horizontal
	U Height	1U
<b>Physical Characteristics</b>	Color	Black
	Enclosure Type	Steel
	Internal Depth	0.8 in [20.2 mm]
	Product Height	1.7 in [43.7 mm]
	Product Weight	14.9 oz [421.2 g]
	Product Width	19.1 in [485 mm]
	Rail Thickness	0 in [1.2 mm]
<b>Packaging Information</b>	Shipping (Package) Weight	17.9 oz [506.4 g]
<b>What's in the Box</b>	Included in Package	1 - 1U Cable Manager
		4 - 10/32 Panel Screws
		4 - 12/24 Panel Screws

Product appearance and specifications are subject to change without notice.