

Composite and S-Video to VGA Video Converter for Computer Monitors

Product ID: COMP2VGA



This Composite and S-Video to VGA Video Converter lets you play console video games on your computer monitor! With StarTech.com's for Computer Monitors Video Game Jockey, there's no more waiting to use the TV. Simply connect your Xbox®, Playstation 2®, GAMECUBE™, Dreamcast™, or other game console to the Video Game Jockey, then plug into your computer monitor, and it's game on!

An economical solution that saves the expense of a separate TV and frees up your workspace, the Composite/S-Video to VGA converter supports full audio pass through via your PC speakers or headphones and switches from PC to game display with the push of a button - the adapter even works when the computer is powered off!

A versatile video solution, the Composite/S-Video to VGA converter is also a great way to connect VCRs, DVD players and camcorders to your monitor.

Backed by StarTech.com's 2-year warranty.

Certifications, Reports and Compatibility



Applications

- Connects any commercial game console or VCR/DVD to a VGA monitor

Features

- Compatible anywhere in the world, with automatic NTSC and PAL video signals detection
- Convenient push-button switching between game display and PC display
- Easy one-time plug and play set up requires no drivers
- Audio pass through with amplified (active) speakers
- Supports composite (RCA) and S-video input
- Also allows VCRs, DVDs and video cameras to connect to monitor
- Includes all necessary cables for instant out of the box set up
- Superior video resolution - 1280 x 1024 @ 60Hz

Hardware	Warranty	2 Years
	Active or Passive Adapter	Active
	Audio	Yes
	AV Input	Composite S-Video
	AV Output	VGA
Performance	Frequency Range	NTSC Horizontal = 31.4685KHz Vertical = 60 Hz PAL Horizontal = 31.25 KHz Vertical = 50 Hz
	Maximum Analog Resolutions	1280 x 1024
	Supported Resolutions	NTSC - 720 x 480 PAL - 720 x 576
Connector(s)	Connector A	1 - 3.5 mm Mini-Jack (3 Position) Female Input 1 - Composite Video (1 x RCA) Female Input 1 - Stereo Audio (2 x RCA) Female Input 1 - S-Video (4 pin, Mini-DIN) Female Input
	Connector B	1 - 3.5 mm Mini-Jack (3 Position) Female Output 1 - VGA (15 pin, High Density D-Sub) Female Output 1 - VGA (15 pin, High Density D-Sub) Male Input
Special Notes / Requirements	System and Cable Requirements	The SPK out port cannot be used with headphones.
Power	Center Tip Polarity	Positive
	Input Current	0.1 A
	Input Voltage	100 ~ 125 AC
	Output Current	0.6A
	Output Voltage	9 DC
	Power Consumption (In Watts)	5.4
	Power Source	AC Adapter Included
Physical Characteristics	Color	Black
	Product Height	1 in [2.5 cm]
	Product Length	6.5 in [16.5 cm]

	Product Width	4 in [10.1 cm]
	Weight of Product	1.7 oz [49 g]
Packaging Information	Package Height	0.4 in [10 mm]
	Package Length	8.7 in [22 cm]
	Package Width	7.9 in [20 cm]
	Shipping (Package) Weight	2 oz [58 g]
	What's in the Box	Included in Package

Product appearance and specifications are subject to change without notice.