

## 7m DisplayPort Cable with Latches - M/M

Product ID: DISPL7M



The DISPL7M DisplayPort Cable with latches provides a secure connection between your DisplayPort-enabled devices and allows for a connection distance of up to 7 meters between your source and display.

With a bandwidth of 10.8Gbps and support for maximum resolutions up to 2560x1600 (WQXGA), as well as optional audio support, this 7-meter DisplayPort cable offers impressive video capability and ensures that digitally protected content is displayed properly, with both HDCP and DPCP capability.

The DISPL7M is backed by StarTech.com's Lifetime Warranty.

### Certifications, Reports and Compatibility



### Applications

- Connecting a DisplayPort display to a PC or other DisplayPort source

### Features

- Molded latching connectors with strain relief
- Offers 7m in cable length
- Designed and manufactured to DisplayPort standards
- Supports the DPCP (DisplayPort Content Protection) standard in addition to HDCP

<b>Hardware</b>	Warranty	Lifetime
	Cable Jacket Type	PVC - Polyvinyl Chloride
	Cable Shield Type	Aluminum-Mylar Foil with Braid
	Connector Plating	Nickel
	Fire Rating	CMG Rated (General Purpose)
<b>Connector(s)</b>	Connector A	1 - DisplayPort (20 pin) Latching Male
	Connector B	1 - DisplayPort (20 pin) Latching Male
<b>Physical Characteristics</b>	Cable Length	7 m [23 ft]
	Color	Black
	Connector Style	Latching
	Product Length	7 m [23 ft]
	Weight of Product	568 g [20.1 oz]
	Wire Gauge	26 AWG
<b>Packaging Information</b>	Package Height	53 mm [2.1 in]
	Package Length	33 cm [13 in]
	Package Quantity	1
	Package Width	25.5 cm [10 in]
	Shipping (Package) Weight	578 g [20.4 oz]
<b>What's in the Box</b>	Included in Package	1 - 7m DisplayPort Cable with Latches - M/M

Product appearance and specifications are subject to change without notice.