

DisplayPort 1.2 Cable with Latches - Certified, 10 ft

Product ID: DISPLPORT10L



This DisplayPort cable provides a secure connection between your DisplayPort equipped devices and is capable of providing higher performance than either HDMI® or dual-link DVI.

The DP cable supports high resolutions of up to 4K x 2K (4096 x 2160, 60Hz) with a maximum HBR2 bandwidth of 21.6Gbps, as well as optional audio support. The cable also supports Multi-Stream Transport (MST) for daisy chaining multiple monitors.

The 10-foot cable is DisplayPort (VESA) certified to support DP 1.2 specifications and ensure a high-quality, reliable connection for all of your DisplayPort devices.

The DISPLPORT10L is backed by a StarTech.com lifetime warranty for guaranteed reliability and ensures that digitally protected content is displayed properly, with both HDCP and DPCP capability.

Certifications, Reports and Compatibility



Applications

- Connecting a DisplayPort display to a PC or other DisplayPort source

Features

- High-resolution support up to 4K x 2K
- Support for High Bit Rate 2 (HBR2) bandwidth of up to 21.6Gbps
- DisplayPort (VESA) certified
- Backward compatible with DisplayPort 1.1
- Designed and manufactured to DisplayPort 1.2 standards
- Supports the DPCP (DisplayPort Content Protection) standard in addition to HDCP
- Molded latching connectors with strain relief

Hardware	Warranty	Lifetime
	Cable Jacket Type	PVC - Polyvinyl Chloride
	Cable Shield Type	Aluminum-Mylar Foil with Braid
	Connector Plating	Nickel
	Fire Rating	CMG Rated (General Purpose)
	Number of Conductors	19
Connector(s)	Connector A	1 - DisplayPort (20 pin) Latching Male
	Connector B	1 - DisplayPort (20 pin) Latching Male
Physical Characteristics	Cable Length	10 ft [3 m]
	Cable OD	0.3 in [7.3 mm]
	Color	Black
	Connector Style	Latching
	Product Length	10 ft [3 m]
	Product Weight	7 oz [199 g]
	Wire Gauge	28 AWG
Packaging Information	Shipping (Package) Weight	7.3 oz [208 g]
What's in the Box	Included in Package	1 - 10 ft DisplayPort™ Cable 1.2 with Latches - M/M

Product appearance and specifications are subject to change without notice.