

20 ft DisplayPort Cable with Latches - M/M

Product ID: DISPLPORT20L



The DISPLPORT20L 20-foot DisplayPort® Cable supports a maximum bandwidth of 10.8 Gbps, and is capable of providing higher performance than either HDMI® or dual link DVI, while supporting next generation multimedia applications with a maximum resolution capability of up to WQXGA (2560×1600).

The cable features latching connectors, with support for two-way display connectivity and optional audio support.

Featuring 26 gauge (AWG) pure copper wire, the cable includes Aluminum and Mylar shielding to help eliminate EMI and RFI interference and maintain signal integrity without any degradation of quality.

This 20-foot DisplayPort cable is both HDCP and DPCP capable, ensuring that digitally protected content is displayed properly on the connected display.

Certifications, Reports and Compatibility



Applications

- Connecting a DisplayPort® display to a PC or other DisplayPort source

Features

- Molded latching connectors with strain relief
- Designed and manufactured to DisplayPort® standards
- Supports the DPCP (DisplayPort Content Protection) standard in addition to HDCP

Hardware	Warranty	Lifetime
	Cable Jacket Type	PVC - Polyvinyl Chloride
	Cable Shield Type	Aluminum-Mylar Foil with Braid
	Connector Plating	Nickel
	Fire Rating	CMG Rated (General Purpose)
	Number of Conductors	19
Connector(s)	Connector A	1 - DisplayPort (20 pin) Latching Male
	Connector B	1 - DisplayPort (20 pin) Latching Male
Physical Characteristics	Cable Length	20 ft [6.1 m]
	Cable OD	0.3 in [8.5 mm]
	Color	Black
	Connector Style	Latching
	Product Length	20 ft [6.1 m]
	Weight of Product	18.1 oz [513 g]
	Wire Gauge	26 AWG
Packaging Information	Package Height	1 in [25 mm]
	Package Length	12.8 in [32.5 cm]
	Package Quantity	1
	Package Width	9.8 in [25 cm]
	Shipping (Package) Weight	18.8 oz [533 g]
What's in the Box	Included in Package	1 - 20 ft DisplayPort® Cable with Latches - M/M

Product appearance and specifications are subject to change without notice.