

35 ft DisplayPort® Cable with Latches - M/M

Product ID: DISPLPORT35L



The DISPLPORT35L 35-foot DisplayPort® cable provides a connection of up to 35ft between a DisplayPort source and a DisplayPort display, supporting resolutions up to 1920x1200, with no loss of signal quality – more than double the typical DisplayPort connection distance limitation of 16ft.

Its 26 gauge (AWG) pure copper wire, and Aluminum and Mylar shielding helps to eliminate EMI and RFI interference, while its small USB-sized latching connectors support two-way display connectivity and optional audio support.

The DISPLPORT35L DisplayPort cable is both HDCP and DPCP capable, ensuring that digitally protected content is displayed properly on the connected display.

Certifications, Reports and Compatibility



Applications

- Connecting a DisplayPort® display to a PC or alternative DisplayPort source

Features

- Molded latching connectors with strain relief
- Supports the DPCP (DisplayPort® Content Protection) standard in addition to HDCP
- Designed and manufactured to DisplayPort standards

Hardware	Warranty	Lifetime
	Cable Jacket Type	PVC - Polyvinyl Chloride
	Cable Shield Type	Aluminum-Mylar Foil with Braid
	Connector Plating	Nickel
	Fire Rating	CMG Rated (General Purpose)
	Number of Conductors	19
Connector(s)	Connector A	1 - DisplayPort (20 pin) Latching Male
	Connector B	1 - DisplayPort (20 pin) Latching Male
Physical Characteristics	Cable Length	35 ft [10.7 m]
	Cable OD	0.3 in [8.5 mm]
	Color	Black
	Connector Style	Latching
	Product Length	35 ft [10.7 m]
	Weight of Product	32.2 oz [912 g]
	Wire Gauge	26 AWG
Packaging Information	Package Height	2.9 in [73 mm]
	Package Length	13 in [33 cm]
	Package Width	8.4 ft [2.6 m]
	Shipping (Package) Weight	32.4 oz [919 g]
What's in the Box	Included in Package	1 - 35 ft DisplayPort® Cable with Latches - M/M

Product appearance and specifications are subject to change without notice.