

Dual-4K Docking Station with 6 x USB 3.0 Ports

Product ID: DK30A2DH



This dual-4K docking station offers wide flexibility in setting up your workstation, working with both USB-C and USB-A port laptops and supporting multiple combinations of Ultra HD 4K DisplayPort and HDMI monitors.

Enhance Productivity with Dual-4K 60Hz Video

Ideal for highly detailed graphics applications, this dual-4K 60Hz docking station enhances your productivity by expanding the display capabilities of your laptop across two Ultra HD 4K monitors. The laptop docking station works with DisplayLink® to support high-resolution monitors, enabling two full 4K 60Hz displays from a single USB connection.

With the dual-4K dock, connect:

- 2x 4K DisplayPort displays (up to 4096 x 2160p @ 60Hz)
- 2x 4K HDMI displays (up to 4096 x 2160p @ 60Hz)
- 1x 4K DisplayPort + 4K HDMI displays (up to 4096 x 2160p @ 60Hz)

Connects to USB-C and USB-A Laptops

The USB 3.0 docking station supports USB-C and USB-A enabled Mac and Windows laptops. This means you can connect newer USB-C or Thunderbolt™ 3 laptops or extend the life of legacy USB 3.0 (Type-A) laptops.

All the Connections You Need

This USB-A & USB-C dock lets you transform your Mac or Windows laptop into a full workstation with six USB 3.0 (Type-A) ports, a Gigabit Ethernet port, and separate 3.5 mm audio and microphone ports for multiple audio connections, all using a single cable.

To add laptop charging support for USB-C-equipped laptops, simply add the StarTech.com HB30C1A1CPD* [USB to USB-C adapter](#).

DK30A2DH is backed by a StarTech.com 3-year warranty and free lifetime technical support.

*Note: USB-C type power adapter is required in conjunction with the HB30C1A1CPD to charge a USB-C laptop.

Certifications, Reports and Compatibility



Applications

- Perfect for laptops in business, government, finance, and sales environments
- Ideal for working with graphics or data-intensive applications on your laptop

Features

- Connect your Mac or Windows laptop to dual-4K 60Hz monitors (2x DisplayPort, 2x HDMI, HDMI + DP)
- DisplayLink certified DL 6950 chipset supports both USB-C and USB-A port equipped PC laptops
- Connect more USB devices with 6 x USB 3.0 (Type-A) ports
- Add wired network connectivity with the Gigabit Ethernet RJ45 port
- Multiple audio connections with separate 3.5 mm headphone and mic input audio jack ports

Hardware	Warranty	3 Years	
	4K Support	Yes	
	Bus Type	USB-C	
		USB 3.0	
	Chipset ID	DisplayLink - DL-6950 VIA/VLI - VL813	
	Displays Supported	2	
	Fast-Charge Port(s)	Yes	
	Industry Standards	IEEE 802.3, IEEE 802.3u, IEEE 802.3ab USB 3.0 - Backward compatible with USB 2.0/1.1	
Performance	Auto MDIX	Yes	
	Compatible Networks	10/100/1000 Mbps	
	Full Duplex Support	Yes	
	Maximum Data Transfer Rate	5 Gbps (USB 3.0) 2 Gbps (Ethernet; Full-Duplex)	
	Maximum Digital Resolutions	Single display - DisplayPort - 4096 x 2160 @ 60Hz / 3840 x 2160 @ 60Hz Single Display - HDMI - 4096 x 2160 @ 60Hz / 3840 x 2160 @ 60Hz Dual displays - DisplayPort and HDMI - 4096 x 2160 @ 60Hz / 3840 x 2160 @ 60Hz	
	Type and Rate	USB 3.0 - 5 Gbit/s	
	UASP Support	Yes	
Connector(s)	Connector Type(s)	2 - DisplayPort Female 2 - HDMI Female 1 - USB Type-C (24 pin) USB 3.0 Female 1 - Ethernet Gigabit Female 6 - 9 pin USB 3.0 A Female 1 - 3.5 mm Audio 1 - Microphone Jack	
	Software	OS Compatibility	Windows® 7, 8, 8.1, 10 macOS 10.11 - 10.12, 10.14
	Special Notes / Requirements	Note	USB 3.0 is also known as USB 3.1 Gen 1; this connectivity standard offers speeds up to 5Gbps. A USB-C to USB-C cable and a USB-C to USB-A cable are included.

		4K resolution is supported on both video ports. A 4K-capable DisplayPort or HDMI display is required to achieve 4Kx2K resolution
	System and Cable Requirements	A host laptop with an available USB-C port or a USB-A port.
Indicators	LED Indicators	1 - Power
Power	Center Tip Polarity	Positive
	Input Current	1 A
	Input Voltage	100 ~ 240 AC
	Output Current	2 A
	Output Voltage	20V DC
	Plug Type	N
	Power Consumption (In Watts)	40W
	Power Source	AC Adapter Included
Environmental	Humidity	10~90% RH
	Operating Temperature	0°C to 40°C (32°F to 104°F)
	Storage Temperature	-10°C to 70°C (14°F to 158°F)
Physical Characteristics	Cable Length	6 in [152.4 mm]
	Color	Black & Silver
	Enclosure Type	Aluminum and Plastic
	Product Height	1.1 in [28 mm]
	Product Length	8.9 in [226 mm]
	Product Weight	10.6 oz [301 g]
	Product Width	3.4 in [87 mm]
Packaging Information	Shipping (Package) Weight	30 oz [851 g]
What's in the Box	Included in Package	<ul style="list-style-type: none"> 1 - docking station 1 - 1 m USB-C to USB-A cable 1 - 1 m USB-C to USB-C cable 1 - universal power adapter (NA/JP, UK, EU, ANZ) 1 - quick-start guide

Product appearance and specifications are subject to change without notice.