

## Dual Monitor USB 3.0 Docking Station - 6x USB 3.0

Product ID: DK30ADD



This USB 3.0 docking station for Mac and Windows™ laptops gives you display flexibility and the ports you need to maximize workstation performance. The cost-effective dual-monitor docking station provides many video output options including HDMI®, DVI and VGA (with adapter), and gives you six USB ports for peripherals, including two fast-charge USB ports.

### Enhance Productivity with Dual Video

The USB 3.0 dock expands the display capabilities of your Mac or Windows laptop. Set up dual displays by connecting to one HDMI and one DVI monitor. Plus, the laptop docking station includes a DVI to VGA adapter, so you can connect to a legacy VGA monitor.

### With the dual-monitor dock, you can connect:

- 1x HDMI display + 1x DVI display at 2048 x 1152 resolution @ 60Hz
- 1x HDMI display at 2048 x 1152 resolution + 1x VGA display at 1920 x 1200 resolution @ 60Hz

## **All the Connections You Need**

Transform your laptop into a fully capable workstation. This USB 3.0 dock provides six USB 3.0 (Type-A) ports so you can easily connect your keyboard, external drives and other peripherals, from the single USB 3.0 host connection. Two of the USB 3.0 ports are always-on fast-charge ports, adding charge-and-sync flexibility for up to two mobile devices. The docking station also provides a Gigabit Ethernet port plus a 3.5 mm audio headphone port.

DK30ADD is backed by a StarTech.com 3-year warranty and free lifetime technical support.

### Certifications, Reports and Compatibility



### Applications

- Connect to a wide range of monitors in businesses and institutions
- Ideal for shared workspaces in hotels, or for short-term hot desk applications
- Add dual video outputs to a laptop, where the video card can't be replaced

### Features

- Connects your Mac or Windows laptop to dual monitors: HDMI + DVI, or HDMI + VGA
- Connect more USB devices with 6x USB 3.0 (Type-A) ports including 2x Fast-Charge ports
- Add wired network connectivity with the Gigabit Ethernet RJ45 port
- DVI to VGA adapter included to connect to a legacy VGA display or projector

<b>Hardware</b>	Warranty	3 Years
	4K Support	No
	Bus Type	USB 3.0
	Chipset ID	DisplayLink - DL-3900 VIA/VLI - VL813
	Displays Supported	2
	Fast-Charge Port(s)	Yes
	Industry Standards	USB Battery Charging Specification Rev. 1.2 IEEE 802.3, IEEE 802.3u, IEEE 802.3ab USB 3.0 - Backward compatible with USB 2.0/1.1
	Interface	USB 3.0
<b>Performance</b>	Auto MDIX	Yes
	Compatible Networks	10/100/1000 Mbps
	Full Duplex Support	Yes
	Maximum Data Transfer Rate	5 Gbps (USB 3.0) 2 Gbps (Ethernet; Full-Duplex)
	Maximum Digital Resolutions	Dual displays - HDMI + DVI - 2048 x 1152 @ 60Hz Dual displays - HDMI 2048 x 1152 + VGA 1920 x 1200 @ 60Hz
	Type and Rate	USB 3.0 - 5 Gbit/s
	UASP Support	Yes
<b>Connector(s)</b>	Connector Type(s)	1 - DVI-I (29 pin) Female 1 - HDMI (19 pin) Female 2 - USB 3.0 A (Fast-Charge, 9 pin, SuperSpeed) Female 4 - USB Type-A (9 pin) USB 3.0 Female 1 - RJ-45 Female 1 - 3.5 mm Mini-Jack (3 Position) Female 1 - USB Type-B (9 pin) USB 3.0 Female
<b>Software</b>	OS Compatibility	Windows® 7, 8, 8.1, 10 macOS 10.10 - 10.12, 10.14
<b>Special Notes / Requirements</b>	<b>Note</b>	USB 3.0 is also known as USB 3.1 Gen 1; this connectivity standard offers speeds up to 5Gbps.  A DVI to VGA adapter is included.
	System and Cable Requirements	A host laptop with an available USB-A port.
<b>Indicators</b>	LED Indicators	1 - Power

<b>Power</b>	Center Tip Polarity	Positive
	Input Current	1 A
	Input Voltage	100 ~ 240 AC
	Output Current	2 A
	Output Voltage	20V DC
	Plug Type	N
	Power Consumption (In Watts)	40W
	Power Source	AC Adapter Included
<b>Environmental</b>	Humidity	10-90% non-condensing
	Operating Temperature	0°C to 40°C (32°F to 104°F)
	Storage Temperature	-10°C to 70°C (14°F to 158°F)
<b>Physical Characteristics</b>	Cable Length	39.4 in [1000 mm]
	Color	Black & Silver
	Enclosure Type	Plastic
	Product Height	1.2 in [31.2 mm]
	Product Length	8.5 in [216.1 mm]
	Product Weight	10.3 oz [291 g]
	Product Width	3.4 in [86.2 mm]
<b>Packaging Information</b>	Shipping (Package) Weight	28.8 oz [815 g]
<b>What's in the Box</b>	Included in Package	1 - docking station
		1 - USB 3.0 cable
		1 - DVI to VGA adapter
		1 - universal power adapter (NA/JP, UK, EU, ANZ)
		1 - quick-start guide

Product appearance and specifications are subject to change without notice.