

# 16.4ft. (5 m) DisplayPort 1.4 Cable - VESA® Certified

Product ID: DP14MM5M



This DisplayPort 1.4 cable connects your DisplayPort™ laptop or desktop computer to a “super ultra-high definition” 8K monitor, TV or projector. It supports resolutions up to 8K (7680x4320) @ 60Hz.

The DisplayPort monitor cable provides the essential connection to support the next generation of super ultra-high definition video.

This cable is VESA® to ensure full compliance and efficient operation of the higher link rate of HBR3. It has been tested to meet all DP 1.4 specifications to ensure quality and reliability.

## The Superior Performance of DisplayPort 1.4

This 8K DisplayPort cable supports all DP 1.4 features:

- High Bit Rate 3 (HBR3) Bandwidths of 32.4 Gbps supporting the latest in industry standards
- High Dynamic Range (HDR) for higher contrast ratio and vivid colors
- Multi-Stream Transport (MST) for daisy-chaining multiple monitors
- Display Stream Compression 1.2 (DSC) for maximum resolution output

- Forward Error Correction to manage data transmission errors
- High-Bandwidth Digital Content Protection (HDCP 2.2) for a secure connection between source and display
- 32 Uncompressed Digital Audio Channels

## Flexible Cable with Reliable Latched Connectors

The cable has a slim professional grade 28 AWG construction that allows for flexible installation while offering superior reliability for a clean quality installation. Each connector features latches that provide secure connections between your devices.

## 8K: Enabling Business Continuity

8K has a resolution of 7680 x 4320 and is also known as 4320p and Super Ultra High Definition (SUHD). It is seen in digital signage and other commercial displays that require the highest available resolution. This cable is backward compatible with 4K and 5K displays making it the perfect peripheral to start futureproofing your cabling infrastructure.

## Comprehensive Product Testing & Expert Technical Support

StarTech.com conducts thorough compatibility and performance testing on all our products to ensure we are meeting or exceeding industry standards and providing high-quality products to our customers. Our local StarTech.com Technical Advisors have a broad product expertise and work directly with StarTech.com Engineers to provide support for our customers both pre and post-sales.

DP14MM5M is backed by a StarTech.com lifetime warranty.

### Certifications, Reports and Compatibility



### Applications

- Delivering visually enriched presentations
- Displaying crisp digital signage walls
- Creating eye-catching visuals for photography, videography, cinematography
- Producing lifelike gaming

### Features

- Deliver best in class 8K video content with a VESA® certified DisplayPort 1.4 cable
- Experience superior DisplayPort video with resolutions of up to 7690 x 4320 at 60Hz with 4:4:4 chroma subsampling
- Enjoy higher contrast ratios and vivid colors with High Dynamic Range (HDR) support
- High quality 28 AWG construction offers a small outer diameter of 4.5mm for discreet installations
- Lifetime warranty and guaranteed reliability

<b>Hardware</b>	Warranty	Lifetime
	Cable Jacket Type	PVC - Polyvinyl Chloride
	Cable Shield Type	Aluminum-Mylar Foil with Braid
	Connector Plating	Gold
	Fire Rating	VW-1 Rated
	Number of Conductors	19
<b>Connector(s)</b>	Connector A	1 - DisplayPort (20 pin) Latching Male
	Connector B	1 - DisplayPort (20 pin) Latching Male
<b>Physical Characteristics</b>	Cable Length	16.4 ft [5 m]
	Color	Black
	Connector Style	Latching
	Product Height	0.4 in [1 cm]
	Product Length	16.4 ft [5 m]
	Product Width	0.5 in [12 mm]
	Weight of Product	14.2 oz [403 g]
	Wire Gauge	28 AWG
<b>Packaging Information</b>	Package Height	0.4 in [10 mm]
	Package Length	12.9 in [32.8 cm]
	Package Width	9.8 in [25 cm]
	Shipping (Package) Weight	14.9 oz [421 g]
<b>What's in the Box</b>	Included in Package	1 - DisplayPort Cable

Product appearance and specifications are subject to change without notice.