

DisplayPort to DVI Dual Link Active Video Adapter Converter - DP to DVI-D - 2560x1600

Product ID: DP2DVID2



The DP2DVID2 DisplayPort® to DVI (Dual-Link) Adapter actively converts the output signal from a DisplayPort video source for use with a DVI-D display (monitor, etc.) or projector, helping to eliminate the equipment costs of upgrading a DVI display to a newer model for the sake of compatibility.

The adapter supports high resolution video (up to 2560x1600 at 60Hz), maintaining the outstanding graphical performance from a DisplayPort-equipped desktop video card, laptop or MacBook®.

DP2DVID2 performs an active DisplayPort-DVI conversion that is suitable for video sources that output either multimode (DP++) or single-mode DisplayPort signals. This ensures the adapter can be used even with graphics cards that aren't capable of outputting multimode DP++ signals, such as ATI® Eyefinity cards.

Back by StarTech.com 3-year warranty, with free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Perfect for larger format screens that use high DVI resolutions with Dual-Link connectivity
- Keep your existing DVI monitor to be used with your new DisplayPort device
- Ideal for using your DVI monitor as a secondary display
- Ideal for digital entertainment centers, home offices, business conference rooms and trade show displays

Features

- Supports resolutions up to 2560x1600 (up to 60Hz) with DVI Dual Link Displays, 1920x1080 (up to 120Hz) with Single-Link DVI displays
- Powered by a USB port
- Supported on any DVI-D display including televisions and Apple Cinema Display HD
- Supports multimode (DP++) and single-mode DisplayPort

Hårdvara	Warranty	3 Years
	Active or Passive Adapter	Aktiv
	Audio	Nej
	AV-ingång	DisplayPort - 1.2
	AV-utgång	DVI
Prestanda	Maximal digital upplösning	2560x1600
	Stöd för widescreen	Ja
	Stödda upplösningar	2560 x 1600 @ 60 Hz 1920 x 1080 @ 120 Hz 1920 x 1200 @ 120 Hz
Kontakt(er)	Connector A	1 - DisplayPort (20-stifts) Hane 1 - USB Type-A (4-stifts) USB 2.0 Hane
	Connector B	1 - DVI-D (25-stifts) Hona
Särskilda anmärkningar/krav	System- och kabelkrav	1 x DVI-D Cable (Destination)
Ström	Power Source	Strömförsörjd via USB
Miljö	Drifttemperatur	0°C to 45°C (32°F to 113°F)
	Förvaringstemperatur	-20°C to 70°C (-4°F to 158°F)
Utseende	Färg	Svart
	Kabellängd	14.6 in [37 cm]
	Kabinetttyp	Av plast
	Produktbredd	2.5 in [64 mm]
	Produkthöjd	0.9 in [2.2 cm]
	Produktlängd	21.6 in [54.9 cm]
	Produktvikt	5.6 oz [160 g]
Förpackning	Fraktvikt (förpackning)	8.2 oz [232 g]
	Package Height	1.4 in [35 mm]
	Package Length	5.6 in [14.3 cm]
	Package Width	6.9 in [17.4 cm]
Vad det är i lådan	Ingår i paketet	1 - DisplayPort to DVI Adapter

Product appearance and specifications are subject to change without notice.