

6 ft DisplayPort to DVI Video Converter Cable - M/M

Product ID: DP2DVIMM6



The DP2DVIMM6 DisplayPort to DVI (M-M) Video Converter Cable lets you connect a DVI capable display to a DisplayPort video card/source using a single cable. The cable provides a connection distance of 6ft and features a male DVI connector and a male DisplayPort connector.

The DisplayPort/DVI video converter cable supports high bandwidth video transmissions, easily delivering monitor resolutions up to 1920x1200 or HDTV resolutions up to 1080p - allowing you to take full advantage of your DVI capable display, while using a cutting edge DisplayPort video source.

DP2DVIMM6 is a passive adapter cable that requires a DP++ port (DisplayPort++), meaning that DVI and HDMI signals can also be passed through the port.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- The DisplayPort to DVI cable allows for an easy and hassle free connection to any DVI-D (digital) display
- Keep your existing DVI display with our DisplayPort to DVI video converter cables

Features

- Supports PC resolutions up to 1920x1200 and HDTV resolutions up to 1080p
- Easy to use cable, no software required

Hardware	Warranty	2 Years
	Active or Passive Adapter	Passive
	Adapter Style	Cable Adapters
	Audio	No
	Cable Jacket Type	PVC - Polyvinyl Chloride
	Connector Plating	Nickel
Performance	Maximum Cable Length	6 ft [1.8 m]
	Maximum Digital Resolutions	1920x1200 / 1080p
Connector(s)	Connector A	1 - DisplayPort (20 pin) Male
	Connector B	1 - DVI-D (25 pin) Male
Special Notes / Requirements	Note	Requires DP++ (DisplayPort++) port from video card or video source.
Physical Characteristics	Cable Length	6 ft [1.8 m]
	Color	Black
	Product Length	72 in [1828 mm]
	Product Weight	5.3 oz [150 g]
Packaging Information	Shipping (Package) Weight	5.6 oz [159 g]
What's in the Box	Included in Package	1 - DisplayPort to DVI Cable

Product appearance and specifications are subject to change without notice.