

DVI to DisplayPort Adapter Converter with Audio - 1920x1200

Product ID: DVI2DPA



The DVI2DPA DVI to DisplayPort Adapter/Converter (with 2-Channel Audio) converts a DVI-D (Digital) single link, Mini-DVI or HDMI source signal and accompanying audio, for use with a DisplayPort monitor.

Supporting resolutions of up to 1920x1200, this USB-powered device offers easy plug-and-play installation with both PC and Mac® platforms, ensuring seamless operation with your DisplayPort display to save the time and hassle of hardware upgrades.

A complete, out-of-the-package solution, this DVI DisplayPort adapter includes all cables necessary for connecting a DVI-D video source and accompanying audio (3.5mm stereo audio) to any DisplayPort monitor, and can also be used with Mini DVI or Mini HDMI sources using additional cables (sold separately - see Accessories).

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Connect a PC DVI or HDMI output to a DisplayPort monitor
- Convert DVI video and audio to one DisplayPort input on monitors that support audio output
- Adapt a DVI-D output signal and connect supporting audio for use with Apple Cinema Displays

Features

- Supports resolutions up to 1920x1200
- USB power, 3.5mm audio and DisplayPort cables included
- Supports stereo audio pass-through to DisplayPort output (DisplayPort audio support required on monitor)
- Stores and passes EDID information
- USB-powered operation
- No software or drivers required

Hardware	Warranty	2 Years
	Audio	Yes
	AV Input	3.5 mm Stereo Audio
		DVI-D
	AV Output	DisplayPort
	Industry Standards	DisplayPort 1.1a DVI 1.0
Performance	Maximum Digital Resolutions	1920x1200
	Wide Screen Supported	Yes
Connector(s)	Connector A	1 - 3.5 mm Mini-Jack (3 Position) Female Input 1 - DVI-D (25 pin) Male Input 1 - USB Mini-B (5 pin) Female
	Connector B	1 - DisplayPort (20 pin) Female Output
Special Notes / Requirements	Note	Can be used with HDMI, mini HDMI or mini DVI input using an adapter - See Accessories
Indicators	LED Indicators	1 - Power indicator
Power	Input Voltage	5 DC
	Power Source	USB-Powered
Environmental	Humidity	10~85% RH
	Operating Temperature	0°C to 70°C (32°F to 158°F)
	Storage Temperature	-10°C to 80°C (14°F to 176°F)
Physical Characteristics	Cable Length	24 in [610 mm]
	Color	Silver
	Enclosure Type	Aluminum and Plastic
	Product Height	0.3 in [6.6 mm]
	Product Length	3 in [76.2 mm]
	Product Weight	7.1 oz [200 g]
	Product Width	2.5 in [63.5 mm]
Packaging Information	Shipping (Package) Weight	0.5 lb [0.2 kg]
What's in the Box	Included in Package	1 - DVI to DisplayPort Converter 1 - 3.5mm Stereo Audio cable

- 1 - DisplayPort cable
- 1 - USB mini B male to USB A male Cable
- 1 - User Manual

Product appearance and specifications are subject to change without notice.