

## DVI to HDMI Video Converter with Audio

Product ID: DVI2HDMIA



The DVI2HDMIA DVI to HDMI® Converter/Adapter lets you connect a DVI-D source with the accompanying RCA audio signal to an HDMI monitor or HDTV, with support for full HD 1080p (1920x1080) resolution.

A cost-effective alternative to upgrading equipment for compatibility, this small form factor adapter provides a plug-and-play solution for connecting your Mac®, PC or home theater device with DVI (digital) output to your television or HDMI monitor. The RCA stereo audio connections integrate the audio signal directly into the HDMI output, so that a single cable can be run to your destination device.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

### Certifications, Reports and Compatibility



### Applications

- Keep your existing HDMI® monitor to be used with your DVI device
- Ideal for digital entertainment centers, home offices, business conference rooms and trade show displays
- Convert your DVI and audio signals for video and audio pass-through to one HDMI cable
- Deliver audio/video content from your PC or Mac to your A/V devices (HDTV or receiver) for a larger and louder viewing

### Features

- DVI-D Video with Audio pass-through to a single HDMI® cable
- Supports HD 1080p (1920x1080) resolution
- Supports 2-channel RCA audio
- Compact design
- Rugged metal enclosure

<b>Hardware</b>	Warranty	2 Years
	Active or Passive Adapter	Active
	Audio	Yes
	AV Input	Audio RCA DVI-D
	AV Output	HDMI
	Industry Standards	Standard HDMI®, HDCP Compliant
<b>Performance</b>	Bandwidth	225MHz
	Maximum Data Transfer Rate	2.25Gbps
	Maximum Digital Resolutions	1080p / 1920x1080
	Supported Resolutions	480i,576i,1080i Interlaced(50-60Hz) 480p,576p,720p,1080p Progressive(50-60Hz)
	Wide Screen Supported	Yes
<b>Connector(s)</b>	Connector Type(s)	1 - DVI-I (29 pin) Female Input 1 - HDMI (19 pin) Female Output 2 - Stereo Audio (2 x RCA) Female Input
	<b>Special Notes / Requirements</b>	<b>Note</b> DVI signal must be DVI-D (digital only).
	<b>Indicators</b>	LED Indicators
<b>Power</b>		Center Tip Polarity
	Input Current	0.5A
	Input Voltage	110V-240V AC
	Output Current	2A
	Output Voltage	5 DC
	Plug Type	M
	Power Consumption (In Watts)	5
<b>Environmental</b>	Power Source	AC Adapter Included
	Humidity	10~85% RH
	Operating Temperature	0°C to 70°C (32°F to 158°F)
<b>Physical Characteristics</b>	Storage Temperature	-10°C to 80°C (14°F to 176°F)
	Color	Black

	Enclosure Type	Steel
	Product Height	2.7 in [68 mm]
	Product Length	3.5 in [88 mm]
	Product Weight	4 oz [113 g]
	Product Width	1 in [25.5 mm]
<b>Packaging Information</b>	Shipping (Package) Weight	12.8 oz [362 g]
<b>What's in the Box</b>	Included in Package	1 - DVI to HDMI converter 1 - Power Adapter 1 - User Manual

Product appearance and specifications are subject to change without notice.