

## 1 ft DVI-D Dual Link Cable - M/M

Product ID: DVIDDMM1



The DVIDDMM1 1ft DVI-D Dual Link cable features 2 male DVI (25-pin) connectors and provides a reliable, purely digital connection between your desktop or laptop computer and a DVI-D monitor or projector.

The 1 ft DVI-D digital monitor cable supports resolutions of up to 2560x1600 and transmission rates of up to 9.9 Gbits/sec and is fully compliant with DVI DDWG standards.

Designed and constructed for maximum durability, this high quality digital video cable is backed by StarTech.com's Lifetime Warranty.

### Certifications, Reports and Compatibility



### Applications

- Connect your desktop or laptop computer to a DVI-D Dual Link display or projector

### Features

- Supports a maximum resolution of 2560x1600
- High-speed digital transmission rate of up to 9.9 Gbits/sec
- Ferrite core eliminates EMI interference
- Aluminum-Mylar Foil with Braided Shielding
- Supports hot-plugging of DVI display devices
- Compliant with DVI DDWG Standards

<b>Hardware</b>	Warranty	Lifetime
	Cable Jacket Type	PVC - Polyvinyl Chloride
	Cable Shield Type	Aluminum-Mylar Foil with Braid
	Connector Plating	Nickel
	Fire Rating	CMG Rated (General Purpose)
	Industry Standards	DVI DDWG Standard
<b>Connector(s)</b>	Connector A	1 - DVI-D (25 pin) Male
	Connector B	1 - DVI-D (25 pin) Male
<b>Physical Characteristics</b>	Cable Length	1 ft [0.3 m]
	Color	Black
	Product Height	16.000
	Product Length	1 ft [0.3 m]
	Product Width	39.600
	Weight of Product	3.2 oz [91.5 g]
	Wire Gauge	28 AWG
<b>Packaging Information</b>	Package Height	0 in [0.1 mm]
	Package Length	8.7 in [22 cm]
	Package Width	7.9 in [20 cm]
	Shipping (Package) Weight	3.6 oz [102 g]
<b>What's in the Box</b>	Included in Package	1 - 1 ft DVI-D Dual Link Cable - M/M

Product appearance and specifications are subject to change without notice.