

1m DVI-D Dual Link Cable – M/M

Product ID: DVIDDMM1M



The DVIDDMM1M 1m DVI-D Dual Link cable features 2 male DVI (25-pin) connectors and provides a reliable, purely digital connection between your desktop or laptop computer and a DVI-D monitor or projector.

The 1m DVI-D digital monitor cable supports resolutions of up to 2560x1600 and transmission rates of up to 9.9 Gbits/sec and is fully compliant with DVI DDWG standards.

Designed and constructed for maximum durability, this high quality digital video cable is backed by StarTech.com's Lifetime Warranty.

Certifications, Reports and Compatibility



Applications

- Connect your desktop or laptop computer to a DVI-D Dual Link display or projector

Features

- Supports a maximum resolution of 2560x1600
- High-speed digital transmission rate of up to 9.9 Gbits/sec
- Ferrite core eliminates EMI interference
- Aluminum-Mylar Foil with Braided Shielding
- Supports hot-plugging of DVI display devices
- Compliant with DVI DDWG Standards

Hardware	Warranty	Lifetime
	Cable Jacket Type	PVC - Polyvinyl Chloride
	Cable Shield Type	Aluminum-Mylar Foil with Braid
	Connector Plating	Nickel
Connector(s)	Connector A	1 - DVI-D (25 pin) Male
	Connector B	1 - DVI-D (25 pin) Male
Physical Characteristics	Cable Length	1 m [3.3 ft]
	Color	Black
	Product Height	16.000
	Product Length	1 m [3.3 ft]
	Product Width	39.600
	Weight of Product	207 g [7.3 oz]
	Wire Gauge	28 AWG
Packaging Information	Package Height	0.1 mm [0 in]
	Package Length	20 cm [7.9 in]
	Package Quantity	1
	Package Width	22 cm [8.7 in]
	Shipping (Package) Weight	0.2 kg [0.5 lb]
What's in the Box	Included in Package	1 - 1m DVI-D Dual Link Monitor Cable - M/M

Product appearance and specifications are subject to change without notice.