

25 ft DVI-D Dual Link Cable - M/M

Product ID: DVIDDMM25



The DVIDDMM25 25ft DVI-D Dual Link cable features 2 male DVI (25-pin) connectors and offers 25 feet in cable length, making it perfect for longer connections between your desktop or laptop computer and a DVI-D monitor or projector.

The 25 ft DVI-D digital monitor cable supports resolutions of up to 2560x1600 and transmission rates of up to 9.9 Gbits/sec and is fully compliant with DVI DDWG standards.

Designed and constructed for maximum durability, this high quality digital video cable is backed by StarTech.com's Lifetime Warranty.

Certifications, Reports and Compatibility



Applications

- Sluit uw desktop of laptop aan op een DVI-D Dual Link-scherm of -projector

Features

- Ondersteuning van resoluties tot 2560x1600
- High-speed digitale transmissiesnelheid tot 9,9 Gbit/sec
- Ferrietkern elimineert EMI-interferentie
- Aluminum-Mylar folie met gevlochten afscherming
- Ondersteunt hot-plugging van DVI-beeldschermen
- Voldoet aan de DVI DDWG-specificaties

Hardware	Warranty	Lifetime
	Aantal ferrieten	2
	Brandbestendigheid	CMG goedgekeurd (algemeen doel)
	Connectormateriaal	Nikkel
	Industriestandaarden	DVI DDWG Standard
	Kabelafscherming	Aluminium-Mylar folie met vlechtwerk
	Type kabelmantel	PVC - Polyvinyl Chloride
Connector(en)	Connector A	1 - DVI-D (25-polig) Mannelijk
	Connector B	1 - DVI-D (25-polig) Mannelijk
Fysieke eigenschappen	Draaddikte	28 AWG
	Gewicht product	26.9 oz [763 g]
	Kabellengte	25 ft [7.6 m]
	Kleur	Zwart
	Lengte product	25 ft [7.6 m]
Verpakkingsinformatie	Package Height	11.8 in [30 cm]
	Package Length	9.4 in [23.8 cm]
	Package Width	2.2 in [56 mm]
	Verzendgewicht (verpakt)	26.9 oz [763 g]
Wat wordt er meegeleverd	Meegeleverd	1 - 25 ft DVI-D Dual Link Cable - M/M

Product appearance and specifications are subject to change without notice.