

## 25 ft DVI-D Dual Link Cable - M/M

Product ID: DVIDDMM25



The DVIDDMM25 25ft DVI-D Dual Link cable features 2 male DVI (25-pin) connectors and offers 25 feet in cable length, making it perfect for longer connections between your desktop or laptop computer and a DVI-D monitor or projector.

The 25 ft DVI-D digital monitor cable supports resolutions of up to 2560x1600 and transmission rates of up to 9.9 Gbits/sec and is fully compliant with DVI DDWG standards.

Designed and constructed for maximum durability, this high quality digital video cable is backed by StarTech.com's Lifetime Warranty.

### Certifications, Reports and Compatibility



### Applications

- Connect your desktop or laptop computer to a DVI-D Dual Link display or projector

### Features

- Supports a maximum resolution of 2560x1600
- High-speed digital transmission rate of up to 9.9 Gbits/sec
- Ferrite core eliminates EMI interference
- Aluminum-Mylar Foil with Braided Shielding
- Supports hot-plugging of DVI display devices
- Compliant with DVI DDWG Standards

<b>Hardware</b>	Warranty	Lifetime
	Cable Jacket Type	PVC - Polyvinyl Chloride
	Cable Shield Type	Aluminum-Mylar Foil with Braid
	Connector Plating	Nickel
	Fire Rating	CMG Rated (General Purpose)
	Industry Standards	DVI DDWG Standard
	Number of Ferrites	2
<b>Connector(s)</b>	Connector A	1 - DVI-D (25 pin) Male
	Connector B	1 - DVI-D (25 pin) Male
<b>Physical Characteristics</b>	Cable Length	25 ft [7.6 m]
	Color	Black
	Product Length	25 ft [7.6 m]
	Weight of Product	26.9 oz [763 g]
	Wire Gauge	28 AWG
<b>Packaging Information</b>	Package Height	11.8 in [30 cm]
	Package Length	9.4 in [23.8 cm]
	Package Width	2.2 in [56 mm]
	Shipping (Package) Weight	26.9 oz [763 g]
<b>What's in the Box</b>	Included in Package	1 - 25 ft DVI-D Dual Link Cable - M/M

Product appearance and specifications are subject to change without notice.