

3m DVI-D Dual Link Cable – M/M

Product ID: DVIDDMM3M



The DVIDDMM3M 3m DVI-D Dual Link cable features 2 male DVI (25-pin) connectors and provides a reliable, purely digital connection between your desktop or laptop computer and a DVI-D monitor or projector.

The 3m DVI-D digital monitor cable supports resolutions of up to 2560x1600 and transmission rates of up to 9.9 Gbits/sec and is fully compliant with DVI DDWG standards.

Designed and constructed for maximum durability, this high quality digital video cable is backed by StarTech.com's Lifetime Warranty.

Certifications, Reports and Compatibility



Applications

- Connect your desktop or laptop computer to a DVI-D Dual Link display or projector

Features

- Supports a maximum resolution of 2560x1600
- High-speed digital transmission rate of up to 9.9 Gbits/sec
- Ferrite core eliminates EMI interference
- Aluminum-Mylar Foil with Braided Shielding
- Supports hot-plugging of DVI display devices
- Compliant with DVI DDWG Standards

Hardware	Warranty	Lifetime
	Cable Jacket Type	PVC - Polyvinyl Chloride
	Cable Shield Type	Aluminum-Mylar Foil with Braid
	Connector Plating	Nickel
	Fire Rating	CMG Rated (General Purpose)
	Industry Standards	DVI DDWG Standard
	Number of Conductors	24
	Number of Ferrites	2
Connector(s)	Connector A	1 - DVI-D (25 pin) Male
	Connector B	1 - DVI-D (25 pin) Male
Physical Characteristics	Cable Length	3 m [9.8 ft]
	Cable OD	8.6 mm [0.3 in]
	Color	Black
	Connector Style	Straight
	Product Length	3 m [9.8 ft]
	Product Weight	290 g [10.2 oz]
	Wire Gauge	28 AWG
Packaging Information	Package Quantity	1
	Shipping (Package) Weight	0.3 kg [0.7 lb]
What's in the Box	Included in Package	1 - 3m DVI-D Dual Link Digital Video Monitor Cable - M/M

Product appearance and specifications are subject to change without notice.