

## 3m DVI-D Dual Link Cable – M/M

Product ID: DVIDDMM3M



The DVIDDMM3M 3m DVI-D Dual Link cable features 2 male DVI (25-pin) connectors and provides a reliable, purely digital connection between your desktop or laptop computer and a DVI-D monitor or projector.

The 3m DVI-D digital monitor cable supports resolutions of up to 2560x1600 and transmission rates of up to 9.9 Gbits/sec and is fully compliant with DVI DDWG standards.

Designed and constructed for maximum durability, this high quality digital video cable is backed by StarTech.com's Lifetime Warranty.

### Certifications, Reports and Compatibility



### Applications

- Connect your desktop or laptop computer to a DVI-D Dual Link display or projector

### Features

- Supports a maximum resolution of 2560x1600
- High-speed digital transmission rate of up to 9.9 Gbits/sec
- Ferrite core eliminates EMI interference
- Aluminum-Mylar Foil with Braided Shielding
- Supports hot-plugging of DVI display devices
- Compliant with DVI DDWG Standards

<b>Hardware</b>	Warranty	Lifetime
	Cable Jacket Type	PVC - Polyvinyl Chloride
	Cable Shield Type	Aluminum-Mylar Foil with Braid
	Connector Plating	Nickel
	Fire Rating	CMG Rated (General Purpose)
	Industry Standards	DVI DDWG Standard
	Number of Conductors	24
	Number of Ferrites	2
<b>Connector(s)</b>	Connector A	1 - DVI-D (25 pin) Male
	Connector B	1 - DVI-D (25 pin) Male
<b>Physical Characteristics</b>	Cable Length	3 m [9.8 ft]
	Cable OD	8.6 mm [0.3 in]
	Color	Black
	Connector Style	Straight
	Product Length	3 m [9.8 ft]
	Product Weight	290 g [10.2 oz]
	Wire Gauge	28 AWG
<b>Packaging Information</b>	Package Quantity	1
	Shipping (Package) Weight	0.3 kg [0.7 lb]
<b>What's in the Box</b>	Included in Package	1 - 3m DVI-D Dual Link Digital Video Monitor Cable - M/M

Product appearance and specifications are subject to change without notice.