

40 ft DVI-D Dual Link Cable - M/M

Product ID: DVIDDMM40



The DVIDDMM40 40ft DVI-D Dual Link cable features 2 male DVI (25-pin) connectors and offers 40 feet in cable length, making it perfect for longer connections between your desktop or laptop computer and a DVI-D monitor or projector.

The 40 ft DVI-D digital monitor cable supports resolutions of up to 2560x1600 and transmission rates of up to 9.9 Gbits/sec and is fully compliant with DVI DDWG standards.

Designed and constructed for maximum durability, this high quality digital video cable is backed by StarTech.com's Lifetime Warranty.

Certifications, Reports and Compatibility



Applications

- Connect your desktop or laptop computer to a DVI-D Dual Link display or projector

Features

- Supports a maximum resolution of 2560x1600
- High-speed digital transmission rate of up to 9.9 Gbits/sec
- Ferrite core eliminates EMI interference
- Aluminum-Mylar Foil with Braided Shielding
- Supports hot-plugging of DVI display devices
- Compliant with DVI DDWG Standards

Hardware	Warranty	Lifetime
	Connector Plating	Nickel
	Industry Standards	DVI DDWG Standard
Connector(s)	Connector A	1 - DVI-D (25 pin) Male
	Connector B	1 - DVI-D (25 pin) Male
Physical Characteristics	Cable Length	40 ft [12.2 m]
	Color	Black
	Product Length	40 ft [12.2 m]
	Weight of Product	2.5 lb [1.1 kg]
	Wire Gauge	28 AWG
Packaging Information	Package Height	2.4 in [60 mm]
	Package Length	8.7 in [22 cm]
	Package Width	8.7 in [22 cm]
	Shipping (Package) Weight	2.5 lb [1.1 kg]
What's in the Box	Included in Package	1 - 40 ft DVI-D Dual Link Cable - M/M

Product appearance and specifications are subject to change without notice.