

6in DVI-D Dual Link Digital Port Saver Extension Cable M/F

Product ID: DVIDEXTAA6IN



The DVIDEXTAA6IN 6-inch DVI-D Port Saver Cable/coupler avoids expensive repairs to a computer or display. It does this by extending the port by 6in, thereby eliminating the weight and stress that would typically be placed on the port by a DVI cable. This is especially useful in an environment where cables are unplugged and re-inserted frequently.

The 6in DVI-D cable supports resolutions of up to 2560x1600 and transmission rates of up to 9.9 Gbits/sec, and is fully compliant with DVI DDWG standards.

Designed and constructed for maximum durability, this high quality video cable is backed by StarTech.com's Lifetime Warranty.

Certifications, Reports and Compatibility



Applications

- Extend a video card or monitor DVI-D port by 6in, to protect against damage from frequent connect/disconnects

Features

- Supports a maximum resolution of 2560x1600
- High-speed digital transmission rate of up to 9.9 Gbits/sec
- Aluminum-Mylar Foil with Braided Shielding
- Supports hot-plugging of DVI display devices
- Compliant with DVI DDWG Standards

Hardware	Warranty	Lifetime
	Cable Jacket Type	PVC - Polyvinyl Chloride
	Cable Shield Type	Aluminum-Mylar Foil with Braid
	Connector Plating	Nickel
Connector(s)	Connector A	1 - DVI-D (25 pin) Male
	Connector B	1 - DVI-D (25 pin) Female
Physical Characteristics	Cable Length	0.5 ft [0.2 m]
	Color	Black
	Product Height	0.6 in [16 mm]
	Product Length	6 in [152.4 mm]
	Product Weight	2.8 oz [79 g]
	Product Width	1.6 in [40 mm]
	Wire Gauge	28 AWG
Packaging Information	Package Quantity	1
	Shipping (Package) Weight	3 oz [84 g]
What's in the Box	Included in Package	1 - 6in DVI-D Dual Link Digital Port Saver Cable M/F

Product appearance and specifications are subject to change without notice.