

3m DVI-D Single Link Cable - M/M

Product ID: DVIDSMM3M



The DVIDSMM3M DVI-D Single Link cable features 2 male DVI (19-pin) connectors and provides a reliable, purely digital connection between your desktop or laptop computer and a DVI-D monitor or projector.

The 3m DVI-D male to male cable supports resolutions of up to 1920x1200 and transmission rates of up to 4.95 Gbits/sec, and is fully compliant with DVI DDWG standards.

Designed and constructed for maximum durability, this high quality digital video cable is backed by StarTech.com's Lifetime Warranty.

Certifications, Reports and Compatibility



Applications

- Connect your desktop or laptop computer to a DVI-D Single Link display or projector

Features

- Supports resolutions up to 1920x1200
- High-speed digital transmission rate of up to 4.95 Gbits/sec
- Aluminum-mylar foil with braided shielding
- Supports hot-plugging of DVI display devices
- Compliant with DVI DDWG Standards

Hardware	Warranty	Lifetime
	Cable Jacket Type	PVC - Polyvinyl Chloride
	Cable Shield Type	Aluminum-Mylar Foil with Braid
	Connector Plating	Nickel
	Industry Standards	DVI DDWG Standard
Connector(s)	Connector A	1 - DVI-D (19 pin) Male
	Connector B	1 - DVI-D (19 pin) Male
Physical Characteristics	Cable Length	3 m [9.8 ft]
	Color	Black
	Connector Style	Straight
	Product Length	3 m [9.8 ft]
	Weight of Product	283 g [10 oz]
	Wire Gauge	28 AWG
Packaging Information	Package Height	37 mm [1.5 in]
	Package Length	22 cm [8.7 in]
	Package Quantity	1
	Package Width	20 cm [7.9 in]
	Shipping (Package) Weight	293 g [10.3 oz]
What's in the Box	Included in Package	1 - 3m DVI-D Single Link Cable - M/M

Product appearance and specifications are subject to change without notice.