

## 6in DVI-I Dual Link Digital Analog Port Saver Extension Cable M/F

Product ID: DVIEXTAA6IN



The DVIEXTAA6IN 6-inch DVI-I Port Saver Cable/coupler avoids expensive repairs to a computer or display. It does this by extending the port by 6in, thereby eliminating the weight and stress that would typically be placed on the port by a DVI cable. This is especially useful in an environment where cables are unplugged and re-inserted frequently.

The 6in DVI-I cable supports resolutions of up to 2560x1600 and transmission rates of up to 9.9 Gbits/sec, and is fully compliant with DVI DDWG standards.

Designed and constructed for maximum durability, this high quality video cable is backed by StarTech.com's Lifetime Warranty.

### Certifications, Reports and Compatibility



### Applications

- Extend a video card or monitor DVI-I port by 6in, to protect against damage from frequent connect/disconnects

### Features

- Supports a maximum resolution of 2560x1600
- High-speed digital transmission rate of up to 9.9 Gbits/sec
- Aluminum-Mylar Foil with Braided Shielding
- Supports hot-plugging of DVI display devices
- Compliant with DVI DDWG Standards
- Supports both analog and digital displays

<b>Hardware</b>	Warranty	Lifetime
	Cable Jacket Type	PVC - Polyvinyl Chloride
	Connector Plating	Gold
	Fire Rating	CMG Rated (General Purpose)
	Industry Standards	DVI DDWG Standard
	Number of Conductors	29
<b>Connector(s)</b>	Connector A	1 - DVI-I (29 pin) Male
	Connector B	1 - DVI-I (29 pin) Female
<b>Physical Characteristics</b>	Cable Length	6 in [152.4 mm]
	Color	Black
	Product Length	6 in [152.4 mm]
	Weight of Product	3 oz [85 g]
	Wire Gauge	28 AWG
<b>Packaging Information</b>	Package Height	0.6 in [16 mm]
	Package Length	8.9 in [22.5 cm]
	Package Width	4.9 in [12.5 cm]
	Shipping (Package) Weight	3.2 oz [90 g]
<b>What's in the Box</b>	Included in Package	1 - 6in DVI-I Dual Link Digital Analog Port Saver Cable

Product appearance and specifications are subject to change without notice.