

15 ft DVI-I Single Link Digital Analog Monitor Cable M/M

Product ID: DVIISMM15



The DVIISMM15 DVI-I Single Link cable features 2 male DVI (23-pin) connectors and provides a reliable connection between your desktop or laptop computer and a DVI-I monitor or projector.

The 15ft DVI-I male to male cable supports resolutions of up to 1920x1200 and transmission rates of up to 4.95 Gbits/sec, and is fully compliant with DVI DDWG standards.

Designed and constructed for maximum durability, this high quality video cable is backed by StarTech.com's Lifetime Warranty.

Certifications, Reports and Compatibility



Applications

- Connect your desktop or laptop computer to a DVI-I Single Link display or projector

Features

- Supports a maximum resolution of 1920x1200
- High-speed digital transmission rate of up to 4.95 Gbits/sec
- Aluminum-Mylar Foil with Braided Shielding
- Ondersteunt hot-plugging van DVI-beeldschermen
- Voldoet aan de DVI DDWG-specificaties
- Supports both analog and digital displays

	Warranty	Lifetime
Hardware	Industriestandaarden	DVI DDWG Standard
Prestaties	Maximale overdrachtsnelheid	4.95 Gbits/sec
Connector(en)	Connector A	1 - DVI-I (23-polig) Mannelijk
	Connector B	1 - DVI-I (23-polig) Mannelijk
Fysieke eigenschappen	Draaddikte	28 AWG
	Kabellengte	15 ft [4.6 m]
	Kleur	Zwart
Verpakkingsinformatie	Verzendgewicht (verpakt)	1.5 lb [0.7 kg]
Wat wordt er meegeleverd	Meegeleverd	1 - 15 ft DVI-I Single Link Digital Analog Monitor Cable M/M

Product appearance and specifications are subject to change without notice.