

6 ft DVI-I Single Link Digital Analog Monitor Cable M/M

Product ID: DVIISM6



The DVIISM6 DVI-I Single Link cable features 2 male DVI (23-pin) connectors and provides a reliable connection between your desktop or laptop computer and a DVI-I monitor or projector.

The 6ft DVI-I male to male cable supports resolutions of up to 1920x1200 and transmission rates of up to 4.95 Gbits/sec, and is fully compliant with DVI DDWG standards.

Designed and constructed for maximum durability, this high quality video cable is backed by StarTech.com's Lifetime Warranty.

Certifications, Reports and Compatibility



Applications

- Connect your desktop or laptop computer to a DVI-I Single Link display or projector

Features

- Supports a maximum resolution of 1920x1200
- High-speed digital transmission rate of up to 4.95 Gbits/sec
- Aluminum-Mylar Foil with Braided Shielding
- Supports hot-plugging of DVI display devices
- Compliant with DVI DDWG Standards
- Supports both analog and digital displays

	Warranty	Lifetime
Hardware	Industry Standards	DVI DDWG Standard
Performance	Maximum Data Transfer Rate	4.95 Gbits/sec
Connector(s)	Connector A	1 - DVI-I (23 pin) Male
	Connector B	1 - DVI-I (23 pin) Male
Physical Characteristics	Cable Length	6 ft [1.8 m]
	Color	Black
	Product Length	6 ft [1.8 m]
	Weight of Product	9.8 oz [278 g]
	Wire Gauge	28 AWG
Packaging Information	Package Height	0.9 in [24 mm]
	Package Length	8.7 in [22 cm]
	Package Width	7.9 in [20 cm]
	Shipping (Package) Weight	10.1 oz [287 g]
What's in the Box	Included in Package	6 ft DVI-I Single Link Digital Analog Monitor Cable M/M

Product appearance and specifications are subject to change without notice.