

## 6 ft DVI-D Single Link Cable - M/M

Product ID: DVIMM6



The DVIMM6 DVI-D Single Link cable features 2 male DVI (19-pin) connectors and provides a reliable, purely digital connection between your desktop or laptop computer and a DVI-D monitor or projector.

The 6ft DVI-D male to male cable supports resolutions of up to 1920x1200 and transmission rates of up to 4.95 Gbits/sec, and is fully compliant with DVI DDWG standards.

Designed and constructed for maximum durability, this high quality digital video cable is backed by StarTech.com's Lifetime Warranty.

### Certifications, Reports and Compatibility



### Applications

- Connect your desktop or laptop computer to a DVI-D Single Link display or projector

### Features

- Supports resolutions up to 1920x1200
- High-speed digital transmission rate of up to 4.95 Gbits/sec
- Aluminum-Mylar Foil with Braided Shielding
- Supports hot-plugging of DVI display devices
- Compliant with DVI DDWG Standards

<b>Hardware</b>	Warranty	Lifetime
	Cable Jacket Type	PVC - Polyvinyl Chloride
	Cable Shield Type	Aluminum-Mylar Foil with Braid
	Connector Plating	Nickel
	Industry Standards	DVI DDWG Standard
<b>Performance</b>	Maximum Data Transfer Rate	4.95 Gbits/sec
<b>Connector(s)</b>	Connector A	1 - DVI-D (19 pin) Male
	Connector B	1 - DVI-D (19 pin) Male
<b>Physical Characteristics</b>	Cable Length	6 ft [1.8 m]
	Color	Black
	Product Height	0.6 in [16 mm]
	Product Length	6 ft [1.8 m]
	Product Weight	5.4 oz [154 g]
	Product Width	1.6 in [40 mm]
	Wire Gauge	28 AWG
<b>Packaging Information</b>	Shipping (Package) Weight	5.8 oz [163 g]
<b>What's in the Box</b>	Included in Package	1 - 6 ft DVI-D Single Link LCD Flat Panel Monitor Cable - M/M

Product appearance and specifications are subject to change without notice.