

6 ft DVI-D Single Link Cable - M/M

Product ID: DVIMM6



The DVIMM6 DVI-D Single Link cable features 2 male DVI (19-pin) connectors and provides a reliable, purely digital connection between your desktop or laptop computer and a DVI-D monitor or projector.

The 6ft DVI-D male to male cable supports resolutions of up to 1920x1200 and transmission rates of up to 4.95 Gbits/sec, and is fully compliant with DVI DDWG standards.

Designed and constructed for maximum durability, this high quality digital video cable is backed by StarTech.com's Lifetime Warranty.

Certifications, Reports and Compatibility



Applications

- Connect your desktop or laptop computer to a DVI-D Single Link display or projector

Features

- Supports resolutions up to 1920x1200
- High-speed digital transmission rate of up to 4.95 Gbits/sec
- Aluminum-Mylar Foil with Braided Shielding
- Supports hot-plugging of DVI display devices
- Compliant with DVI DDWG Standards

Hardware	Warranty	Lifetime
	Cable Jacket Type	PVC - Polyvinyl Chloride
	Cable Shield Type	Aluminum-Mylar Foil with Braid
	Connector Plating	Nickel
	Industry Standards	DVI DDWG Standard
Performance	Maximum Data Transfer Rate	4.95 Gbits/sec
Connector(s)	Connector A	1 - DVI-D (19 pin) Male
	Connector B	1 - DVI-D (19 pin) Male
Physical Characteristics	Cable Length	6 ft [1.8 m]
	Color	Black
	Product Height	0.6 in [16 mm]
	Product Length	6 ft [1.8 m]
	Product Weight	5.4 oz [154 g]
	Product Width	1.6 in [40 mm]
	Wire Gauge	28 AWG
Packaging Information	Shipping (Package) Weight	5.8 oz [163 g]
What's in the Box	Included in Package	1 - 6 ft DVI-D Single Link LCD Flat Panel Monitor Cable - M/M

Product appearance and specifications are subject to change without notice.