

2 Port ExpressCard 1394a FireWire Laptop Adapter Card

Product ID: EC13942A2



The EC13942A2 (2 Port) ExpressCard Laptop 1394a Firewire Adapter Card provides a stable platform for virtually any FireWire 400 device connection.

Ensuring seamless operation with peripherals connected through FireWire 400, the ExpressCard 1394a FireWire Adapter supports data transfer rates at up to 400Mbps - an ideal solution for connecting FireWire-capable multimedia devices, editing multimedia content or simply transferring large volumes of data from a computer to FireWire-connected external storage.

As an added convenience, the 2-port FireWire card is packaged with a FireWire cable.

This 2 port ExpressCard IEEE 1394a FireWire 400 Laptop adapter card is designed to fit a 34mm ExpressCard slot and is backed by a StarTech.com lifetime warranty.

Certifications, Reports and Compatibility



Applications

- Add a high-speed FireWire port to a laptop without any FireWire ports
- Connect a digital camera to a laptop with an ExpressCard slot to download photos and video
- Connect a high-speed external hard drive to an ExpressCard-enabled system

Features

- Two external FireWire400 ports with support for transfer rates up to 400 Mbps
- 34mm ExpressCard/34 form factor
- Optional external power support for high-powered FireWire devices
- Complaint with IEEE 1394-1995, 2000, OHCI 1.1 standards
- Compliant with ExpressCard revision 1.0 standards
- Plug-and-Play and Hot-Swap compatible

| | | |
|---------------------------------|---------------------------|---|
| Hardware | Warranty | Lifetime |
| | Bus Type | ExpressCard |
| | Card Type | 34mm ExpressCard |
| | Chipset ID | VIA/VLI - VT6315 |
| | Interface | FireWire 400 (1394a) |
| | Ports | 2 |
| Performance | Type and Rate | FireWire 400 IEEE-1394a - 400 Mbit/s |
| Connector(s) | Connector Type(s) | 1 - ExpressCard (34mm) |
| | External Ports | 2 - FireWire 400 (6 pin, IEEE 1394a) Female |
| Software | OS Compatibility | Windows® 2000, XP, Vista, 7, 8, 8.1, 10 Windows Server® 2003, 2008 R2 Mac OS® 10.6 to 10.11 Linux 3.5.x to 4.11.x <i>LTS Versions only</i> |
| Power | Center Tip Polarity | Positive |
| | Output Current | 1A |
| | Output Voltage | 12 DC |
| | Plug Type | H |
| | Power Source | Not Included (not required for standard applications) |
| Environmental | Humidity | 5~85% RH |
| | Operating Temperature | 0°C to 50°C (32°F to 122°F) |
| | Storage Temperature | -20°C to 60°C (-4°F to 140°F) |
| Physical Characteristics | Product Height | 0.6 in [14 mm] |
| | Product Length | 4.5 in [115 mm] |
| | Product Weight | 1 oz [29 g] |
| | Product Width | 1.6 in [40 mm] |
| Packaging Information | Shipping (Package) Weight | 4.1 oz [117 g] |
| What's in the Box | Included in Package | 1 - 2 Port FireWire ExpressCard Adapter 1 - Firewire Cable 1 - Instruction Manual |

Product appearance and specifications are subject to change without notice.