

2m Shielded External eSATA Cable M/M

Product ID: ESATA2M



The ESATA2M 2m Shielded eSATA cable provides a high quality connection between your desktop or laptop computer and an external SATA storage device, and is compliant with SATA III specifications, supporting data transfer rates of up to 6 Gbps.

Designed for optimum performance and reliability, this 2m eSATA cable is backed by our lifetime warranty.

Certifications, Reports and Compatibility



Applications

- Connect your desktop or laptop computer to an external SATA storage device (e.g. external eSATA hard drive)

Features

- 2x eSATA connectors
- Supports full SATA 3.0 6Gbps bandwidth

Hardware	Warranty	Lifetime
	Cable Jacket Type	PVC - Polyvinyl Chloride
	Cable Shield Type	Aluminum-Mylar Foil with Braid
Connector(s)	Connector A	1 - eSATA (7 pin, Data) Receptacle
	Connector B	1 - eSATA (7 pin, Data) Receptacle
Physical Characteristics	Cable Length	2 m [6.6 ft]
	Color	Black
	Product Length	2 m [6.6 ft]
	Weight of Product	132 g [4.7 oz]
	Wire Gauge	26 AWG
Packaging Information	Package Height	10 mm [0.4 in]
	Package Length	22.3 cm [8.8 in]
	Package Quantity	1
	Package Width	12.2 cm [4.8 in]
	Shipping (Package) Weight	135 g [4.8 oz]
What's in the Box	Included in Package	1 - 2m Shielded External eSATA Cable M/M

Product appearance and specifications are subject to change without notice.