

## 2m Shielded External eSATA Cable M/M

Product ID: ESATA2M



The ESATA2M 2m Shielded eSATA cable provides a high quality connection between your desktop or laptop computer and an external SATA storage device, and is compliant with SATA III specifications, supporting data transfer rates of up to 6 Gbps.

Designed for optimum performance and reliability, this 2m eSATA cable is backed by our lifetime warranty.

### Certifications, Reports and Compatibility



### Applications

- Connect your desktop or laptop computer to an external SATA storage device (e.g. external eSATA hard drive)

### Features

- 2x eSATA connectors
- Supports full SATA 3.0 6Gbps bandwidth

<b>Hardware</b>	Warranty	Lifetime
	Cable Jacket Type	PVC - Polyvinyl Chloride
	Cable Shield Type	Aluminum-Mylar Foil with Braid
<b>Connector(s)</b>	Connector A	1 - eSATA (7 pin, Data) Receptacle
	Connector B	1 - eSATA (7 pin, Data) Receptacle
<b>Physical Characteristics</b>	Cable Length	2 m [6.6 ft]
	Color	Black
	Product Length	2 m [6.6 ft]
	Product Weight	132 g [4.7 oz]
	Wire Gauge	26 AWG
<b>Packaging Information</b>	Package Quantity	1
	Shipping (Package) Weight	135 g [4.8 oz]
<b>What's in the Box</b>	Included in Package	1 - 2m Shielded External eSATA Cable M/M

Product appearance and specifications are subject to change without notice.