

3 ft eSATA and USB A to Power eSATA Cable - M/M

Product ID: ESATAUSBMM3



This eSATA and USB A Male to Power eSATA Cable provides a 3ft connection between an external drive enclosure equipped with a power eSATA port and the eSATA and USB port on a PC/Notebook, providing both power (through USB) and data (through SATA) using a single cable.

Expertly designed and constructed of only top quality materials, the 3ft eSATA and USB A Male to Power eSATA Male cable is backed by StarTech.com's Lifetime Warranty.

Certifications, Reports and Compatibility



Applications

- Connect your Powered eSATA device to your PC or Notebook even if you do not have a Powered eSATA port

Features

- 1x eSATA 11-pin Power receptacle
- 1x eSATA 7-pin Data receptacle
- 1x USB-A male connector
- Supports full SATA 3.0 6Gbps bandwidth

	Warranty	Lifetime
Hårdvara	Kabelmanteltyp	PVC - Polyvinyl Chloride
Kontakt(er)	Connector A	1 - Power eSATA (11-stifts, eSATA/USB, 5/12 V) Honuttag
	Connector B	1 - eSATA (7-stifts, data) Honuttag
		1 - USB Type-A (4-stifts) USB 2.0 Hane
Miljö	Drifttemperatur	-20°C to 50°C (-4°F to 122°F)
	Förvaringstemperatur	-20°C to 60°C (-4°F to 140°F)
	Luftfuktighet	60~75% RH
Utseende	Färg	Svart
	Kabellängd	3 ft [0.9 m]
	Produktlängd	3 ft [0.9 m]
	Produktvikt	3 oz [84.6 g]
Förpackning	Fraktvikt (förpackning)	3.1 oz [87.3 g]
Vad det är i lådan	Ingår i paketet	1 - 3ft USB and ESATA to Power eSATA

Product appearance and specifications are subject to change without notice.