

3 ft eSATA and USB A to Power eSATA Cable - M/M

Product ID: ESATAUSBMM3



This eSATA and USB A Male to Power eSATA Cable provides a 3ft connection between an external drive enclosure equipped with a power eSATA port and the eSATA and USB port on a PC/Notebook, providing both power (through USB) and data (through SATA) using a single cable.

Expertly designed and constructed of only top quality materials, the 3ft eSATA and USB A Male to Power eSATA Male cable is backed by StarTech.com's Lifetime Warranty.

Certifications, Reports and Compatibility



Applications

- Connect your Powered eSATA device to your PC or Notebook even if you do not have a Powered eSATA port

Features

- 1x eSATA 11-pin Power receptacle
- 1x eSATA 7-pin Data receptacle
- 1x USB-A male connector
- Supports full SATA 3.0 6Gbps bandwidth

| | | |
|---------------------------|-------------------------|---|
| | Warranty | Lifetime |
| Hårdvara | Kabelmanteltyp | PVC - Polyvinyl Chloride |
| Kontakt(er) | Connector A | 1 - Power eSATA (11-stifts, eSATA/USB, 5/12 V) Honuttag |
| | Connector B | 1 - eSATA (7-stifts, data) Honuttag |
| | | 1 - USB Type-A (4-stifts) USB 2.0 Hane |
| Miljö | Drifttemperatur | -20°C to 50°C (-4°F to 122°F) |
| | Förvaringstemperatur | -20°C to 60°C (-4°F to 140°F) |
| | Luftfuktighet | 60~75% RH |
| Utseende | Färg | Svart |
| | Kabellängd | 3 ft [0.9 m] |
| | Produktlängd | 3 ft [0.9 m] |
| Förpackning | Fraktvikt (förpackning) | 0.2 lb [0.1 kg] |
| Vad det är i lådan | Ingår i paketet | 1 - 3ft USB and ESATA to Power eSATA |

Product appearance and specifications are subject to change without notice.