

## 3 ft eSATA and USB A to Power eSATA Cable - M/M

Product ID: ESATAUSBMM3



This eSATA and USB A Male to Power eSATA Cable provides a 3ft connection between an external drive enclosure equipped with a power eSATA port and the eSATA and USB port on a PC/Notebook, providing both power (through USB) and data (through SATA) using a single cable.

Expertly designed and constructed of only top quality materials, the 3ft eSATA and USB A Male to Power eSATA Male cable is backed by StarTech.com's Lifetime Warranty.

### Certifications, Reports and Compatibility



### Applications

- Connect your Powered eSATA device to your PC or Notebook even if you do not have a Powered eSATA port

### Features

- 1x eSATA 11-pin Power receptacle
- 1x eSATA 7-pin Data receptacle
- 1x USB-A male connector
- Supports full SATA 3.0 6Gbps bandwidth

	Warranty	Lifetime
<b>Hardware</b>	Cable Jacket Type	PVC - Polyvinyl Chloride
<b>Connector(s)</b>	Connector A	1 - Power eSATA (11 pin, eSATA/USB, 5/12V) Receptacle
	Connector B	1 - eSATA (7 pin, Data) Receptacle
		1 - USB Type-A (4 pin) USB 2.0 Male
<b>Environmental</b>	Humidity	60~75% RH
	Operating Temperature	-20°C to 50°C (-4°F to 122°F)
	Storage Temperature	-20°C to 60°C (-4°F to 140°F)
<b>Physical Characteristics</b>	Cable Length	3 ft [0.9 m]
	Color	Black
	Product Length	3 ft [0.9 m]
	Product Weight	3 oz [84.6 g]
<b>Packaging Information</b>	Shipping (Package) Weight	3.1 oz [87.3 g]
<b>What's in the Box</b>	Included in Package	1 - 3ft USB and ESATA to Power eSATA

Product appearance and specifications are subject to change without notice.