

## 40x10mm Replacement Dual Ball Bearing Computer Case Fan w/ LP4

Product ID: FAN4X1LP4



This 40mmx10mm PC computer cooling fan is a perfect addition or replacement PC fan for maintaining suitable operating temperatures within your computer case.

The PC fan can be powered through a simple LP4 connection to the PC power supply and offers a dual ball bearing design to ensure quiet, dependable operation.

### Certifications, Reports and Compatibility



### Applications

- Replace a noisy or failed computer case fan
- Install into a computer chassis to increase air flow and cooling

### Features

- Dual ball bearing design
- Inline LP4 power connectors

<b>Hardware</b>	Warranty	2 Years
	Fan Bearing Type	Ball Bearing
	Number of Conductors	2
<b>Performance</b>	Air Flow Rate	5.22 CFM
	Fan RPM	5000
	Noise Level	23 dBA
<b>Connector(s)</b>	Connector Type(s)	1 - LP4 (4 pin; Large Drive Power) Female 1 - LP4 (4 pin; Large Drive Power) Male
<b>Power</b>	Input Voltage	12 DC
<b>Environmental</b>	Operating Temperature	-10 to 80
<b>Physical Characteristics</b>	Color	Black
	Enclosure Type	Plastic
	Product Height	1.6 in [4 cm]
	Product Length	1.6 in [40 mm]
	Product Width	0.4 in [10 mm]
	Weight of Product	0.7 oz [21 g]
<b>Packaging Information</b>	Package Height	1.3 in [32 mm]
	Package Length	4.5 in [11.5 cm]
	Package Width	2.6 in [67 mm]
	Shipping (Package) Weight	1.3 oz [36 g]
<b>What's in the Box</b>	Included in Package	1 - 4 cm Case Fan

Product appearance and specifications are subject to change without notice.