

# 1U Low Profile 70mm Socket 775 CPU Cooler Fan w/ Heatsink & TX3

Product ID: FAN7751U



This Low Profile 70mm Socket 775 CPU Cooler Fan is designed specifically for use with processors in rack-mounted and low profile mini systems.

Suitable for Dual Core and high-speed Pentium 4 processors, the low profile Socket 775 CPU Fan is compatible with Intel Socket LGA775 P4 (up to 3.8 GHz) and Dual Core processors and features a dual ball-bearing 70mm fan for exceptional cooling and extended service life.

The CPU fan also features a built-on all-copper base skive fin heatsink and includes our thermal CPU paste that helps the cooling capability of the CPU cooler by thermally bonding the CPU to the heatsink for greater dissipation.

Powered through a simple TX3 connection to the computer power supply, the Socket 775 CPU cooler is backed by 2-year warranty.

### Certifications, Reports and Compatibility



### Applications

- Building a Socket 775-based 1U rack mount server
- Replace the stock/OEM cooler for a Socket 775 system

### Features

- Dual ball-bearing 70mm cooling fan
- All copper base, skive-fin heatsink

<b>Hardware</b>	Warranty	2 Years
	Fan Bearing Type	Ball Bearing
	Fan Dimensions (Number / Dimensions)	70 x 70 x 10 mm (2.76 x 2.76 x .39 in.)
	Heatsink Dimensions	3.58 x 3.58 x .55 in. ( 91 x 91 x 14 mm)
<b>Performance</b>	Air Flow Rate	30.79 CFM
	Fan RPM	4500 +/- 10% RPM
	MTBF	50,000 Hours
	Noise Level	< 39 dBA
<b>Connector(s)</b>	Connector Type(s)	1 - Molex Fan (3 pin, TX3) Female
<b>Power</b>	Input Voltage	12 DC
<b>Physical Characteristics</b>	Color	Black
	Product Height	0.9 in [24 mm]
	Product Length	3.7 in [95 mm]
	Product Weight	17.4 oz [493 g]
	Product Width	3.7 in [95 mm]
<b>Packaging Information</b>	Shipping (Package) Weight	1.3 lb [0.6 kg]
<b>What's in the Box</b>	Included in Package	1 - Heatsink Fan assembly
		1 - Backing Plate
		1 - Thermal Compound
		4 - Mounting Screw/Nut
		1 - Instruction Manual

Product appearance and specifications are subject to change without notice.