

70x15mm Replacement Ball Bearing Computer Case Fan w/ TX3 Connector

Product ID: FAN7X15TX3



This versatile 70mm fan is an ideal replacement fan for keeping your computer running cool. The fan can be powered through a TX3 connection, and features a dual ball bearing design that ensures reliable cooling and longer fan lifespan.

The fan can be used to replace the fan component of some CPU coolers or mounted to the side panel of a computer case and features a tachometer pin on the TX3 motherboard connector that provides the host system with fan operating status information.

Certifications, Reports and Compatibility



Applications

- Replace a noisy or failed computer case fan
- Install into a computer to increase air flow and cooling

Features

- Dual ball bearing design
- 3-pin connector with tachometer wire

| | | |
|---------------------------|----------------------------|---|
| | Warranty | 2 Years |
| Hårdvara | Fläktlagerstyp | Kullager |
| Prestanda | Bullernivå | < 34 dBA |
| | Fläkt rpm | 3500 |
| | Luftflödes hastighet | 29.58 CFM |
| | Medeltid mellan fel (MTBF) | 50,000 Hours |
| Kontakt(er) | Kontakttyp(er) | 1 - Molex-fläkt (3-stifts, TX3) Hona |
| Ström | Inspänning | 12 DC |
| | Inström | 26 mA |
| | Strömförbrukning | 3.12W |
| Miljö | Drifttemperatur | -10°C to 70°C (14°F to 158°F) |
| | Förvaringstemperatur | -40°C to 75°C (-40°F to 167°F) |
| | Luftfuktighet | 0~65% RH |
| Utseende | Färg | Svart |
| | Kabinettyp | Av plast |
| | Produktbredd | 0.6 in [15 mm] |
| | Produkthöjd | 2.8 in [70 mm] |
| | Produktlängd | 2.8 in [70 mm] |
| | Produktvikt | 1.3 oz [38 g] |
| Förpackning | Fraktvikt (förpackning) | 0.2 lb [0.1 kg] |
| Vad det är i lådan | Ingår i paketet | 1 - 7cm Case Fan 4 - Mounting Screws |

Product appearance and specifications are subject to change without notice.