

Ceiling TV Mount for Back-to-Back Displays - 3.5' to 5' Pole

Product ID: FPCEILBTB



Create impressive and effective digital signage with this ceiling TV mount, suspending two 32" to 75" TVs, back-to-back. Ideal for open spaces in retail, hospitality, restaurants and many other areas, the dual-screen mount provides a versatile way to inform customers, and doubles the audience viewing your content.

Back-to-Back TV Mount

The dual-screen mount securely holds two flat-screen TVs back to back, in landscape position. The steel mount supports VESA mount displays up to 600 x 400 mm with a weight capacity of 99 lb. (45 kg) per display.

Adjustable Height

With a telescopic pole, the ceiling TV mount lets you suspend two displays at your desired distance from the ceiling, working with a range of ceiling heights. The pole-mount TV bracket can extend from 41.7" to 61.4" (1060 to 1560 mm), with a total lift (height extension) of 19.7" (500 mm).

Easy Screen Adjustment

For optimum viewing, the mount lets you swivel the display +180/-180 degrees around the pole. The free-tilting design lets you adjust the tilt angle +5/-20 degrees.

Swivels to Suit Your Ceiling

The dual-display mount accommodates a wide variety of ceiling types. Swivel the ceiling TV mount to work with virtually any type of ceiling for level viewing, including sloped ceilings (up to 60 degrees) or horizontal (flat) ceilings.

Simple Setup and Cable Management

The ceiling mount provides a hook-and-mount design for easy setup. The wire-management channels keep cables concealed.

FPCEILBTB is backed by a StarTech.com 5-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Set up back-to-back TVs in retail, healthcare, hospitality and other areas
- Keep your guests informed and entertained
- Ideal for digital signage, menu boards, and other applications

Features

- Save space with this ceiling TV mount, suspending two 32" to 75" TVs back to back
- Easy height adjustment with min-max pole length extension of 42" to 61" (1060 to 1560 mm)
- Flexible ceiling TV mount swivels +60°/-60° to adjust to sloped or level ceilings
- Swivel the display +180°/-180° around the pole and tilt +5°/-20°
- Steel mount supports up to 99 lb. (45 kg) per display

Hardware	Warranty	5 Years
	# of Displays Supported	2
	Cable Management	Yes
	Mounting Options	Ceiling Mount
	VESA Hole Pattern(s)	200x200 mm
		300x300 mm
		400x200 mm
400x400 mm		
600x400 mm		
Wallmountable	No	
Performance	Anti-theft	No
	Display Rotation	360°
	Display Tilt	+5° / -20°
	Height Adjustment	Yes
	Maximum Display Size	75"
	Maximum Height	61.4 in [1560 mm]
	Minimum Display Size	32"
	Minimum Height	41.7 in [1060 mm]
	Swivel / Pivot	+180° to -180°
	Video Wall	No
Weight Capacity (Per Display)	99.5 lb [45 kg]	
Physical Characteristics	Color	Black
	Enclosure Type	Steel
	Product Height	32.9 in [83.5 cm]
	Product Length	26.8 in [68 cm]
	Product Width	6.5 in [16.5 cm]
	Weight of Product	21.7 lb [9.8 kg]
Packaging Information	Package Height	5.7 in [14.5 cm]
	Package Length	36.8 in [93.5 cm]
	Package Width	12.2 in [31 cm]

	Shipping (Package) Weight	24 lb [10.8 kg]
What's in the Box	Included in Package	<ul style="list-style-type: none"> 1 - Upper Pole (with Ceiling Mount) 1 - Lower Pole 1 - TV Mount 4 - Vertical Brackets 2 - Horizontal Brackets 2 - M5 x 55 Screws 2 - Nuts 8 - M5 x 14 Screws 8 - M6 x 14 Screws 8 - M6 x 30 Screws 8 - M8 x 30 Screws 8 - M8 x 50 Screws 8 - Rectangular Washers 4 - Round Washers 16 - Small Spacers 16 - Large Spacers 4 - Ceiling Mounting Screws 4 - Concrete Anchors 1 - Wrench 1 - Hex Key 1 - Mounting Template 1 - User Manual

Product appearance and specifications are subject to change without notice.